

Radar measurement Time-of-Flight Micropilot FMR50

Basic model for level liquid applications



More information and current pricing:

www.au.endress.com/FMR50

Benefits:

- Reliable non-contact measurement even for changing product and process conditions
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Highest reliability even in the presence of obstructions in the vessel due to new Multi-Echo Tracking evaluation
- Hardware and software developed according to IEC 61508 up to SIL3 (in homogeneous redundancy)
- Heartbeat Technology for a cost-effective and safe plant operation during the entire life cycle
- Seamless integration into control or asset management systems and intuitive, menu-guided operation concept (on-site or via the control system)
- World's easiest proof test concept for SIL and WHG saves time and cost

Specs at a glance

- **Accuracy** +/- 2 mm (0.08 in)
- **Process temperature** -40...+130 °C (-40...+266 °F)
- **Process pressure absolute / max. overpressure limit** Vacuum...3 bar (Vacuum...43.5 psi)
- **Max. measurement distance** Max. measurement distance
- **Main wetted parts** PVDF, Viton, PP, PBT

Field of application: Micropilot FMR50 is the best choice in simple reservoir and storage applications as well as in utility processes. The FMR50 free space radar is used for continuous, non-contact level measurement of liquids, pastes and slurries. The measurement is not affected by changing media, temperature changes, gas blankets or

vapors. Remote access with SmartBlue app via Bluetooth module is available.

Features and specifications

Continuous / Liquids

Measuring principle

Level radar

Characteristic / Application

For basic level measurement in liquids, pastes and slurries; non affected by changing media, temperature changes, gas blankets or vapor;

Encapsulated PVDF or PP clad horn antenna

Specialities

Heartbeat Technology,

SIL 2 according to IEC 61508,

Bluetooth® commissioning,

Operation and maintenance SmartBlue App,

Safety and reliability with Multi-Echo Tracking,

HistoROM,

RFID TAG for easy identification

Supply / Communication

2-wire (HART / PROFIBUS PA/ FOUNDATION Fieldbus)

4-wire (HART)

Bluetooth® wireless technology and App (optional)

Frequency

K-band (~26 GHz)

Continuous / Liquids**Accuracy**

+/- 2 mm (0.08 in)

Ambient temperature

-40...+80 °C

(-40...+176 °F)

Process temperature

-40...+130 °C

(-40...+266 °F)

Process pressure absolute / max. overpressure limit

Vacuum...3 bar

(Vacuum...43.5 psi)

Main wetted parts

PVDF, Viton, PP, PBT

Process connection

Thread:

G1 1/2, MNPT1 1/2

Flange:

UNI DN80...DN150 (3"...6")

Application

Application

Max. measurement distance

Max. measurement distance

Continuous / Liquids

Communication

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Bluetooth® wireless technology

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, KC

Safety approvals

Overfill protection WHG

SIL

Options

Display,

Customized parameterization,

PWIS free,

Remote operation via SmartBlue App using Bluetooth®

Application limits

Application limits

More information www.au.endress.com/FMR50