

# iTEMP TMT188

## Temperature head transmitter

Transformation of the sensor signal into a stable and standardized output signal for all industries



### Benefits:

- High accuracy in complete ambient temperature range
- Failure information when sensor breaks or short circuits as per NAMUR NE 43
- EMC as per NAMUR NE 21, CE
- Ex approval: ATEX Ex ia and dust zone 22 in compliance with EN 50281-1; FM IS; CSA IS
- UL recognized component to UL 3111-1
- Marine approval
- Galvanic isolation

### Specs at a glance

- **Accuracy** (Type K)  $\leq 0,5$  K (Type K)  $\leq 0,9$  °F

from **A\$162.00**

Price as of 28.11.2022

More information and current pricing:

[www.au.endress.com/TMT188](http://www.au.endress.com/TMT188)

**Field of application:** The transmitter is designed for the transformation of a thermocouple (TC) sensor signal in a fixed measuring range. The standardized output signal used for process measurement is a 4 to 20 mA signal. This means fast, easy and cost-saving temperature measuring as well as reliable and precise measured values for a wide range of industry applications.

### Features and specifications

Temperature transmitters

Measuring principle

Head transmitter

---

**Temperature transmitters****Input**1 x TC

---

**Output**1 x analog 4...20 mA

---

**Auxiliary power supply**

8...35 V DC (standard-version)

8...30 V DC (Ex-version)

---

**Installation**Terminal head form B

---

**Accuracy**(Type K)  $\leq 0,5$  K(Type K)  $\leq 0,9$  °F

---

**Galvanic isolation**yes

---

**Certification**

UL Ex IS

UL Ex NI

GOST Ex i

GL marine approval

GOST Metrology

FM IS,NI,Class I,Div.1+2,Group ABCD

CSA IS,NI,Class I,Div.1+2,Group ABCD

ATEX II1G EEx ia IIC T4/T5/T6

ATEX II3G Ex nA IIC T4/T5/T6

ATEX II3D

ATEX II1G EEx ia IIC T6, II3D

ATEX II3G Ex nA IICT6, II3D

FM+CSA IS,NI,Class I,Div.1+2,Group

ABCD

CSA General Purpose

EAC Ex ia IIC T6 Ga

GL (German Lloyd)

---

More information [www.au.endress.com/TMT188](http://www.au.endress.com/TMT188)