

# TST90

## Modular RTD thermometer

Comprehensive and common temperature measurement technology for almost all branches of industry



More information and current pricing:

[www.au.endress.com/TST90](http://www.au.endress.com/TST90)

### Benefits:

- Fast replaceability of the insert
- High degree of insert compatibility and design as per DIN 43772
- Fast response time with reduced tip

### Specs at a glance

- **Accuracy** +/- 0.05 K (referring to delta-T)
- **Response time** depending on configuration  $t_{50} = 10\text{ s}$   $t_{90} = 31\text{ s}$
- **Max. process pressure (static)** at 20 °C: 50 bar (725 psi)
- **Operating temperature range** PT 100: -50 °C ...200 °C (-58 °F ...392 °F)
- **Max. immersion length on request** up to 4.000,00 mm (157,48")

**Field of application:** The thermometer is mainly used in the chemical industry but also finds its use in other branches. The device is used for high-precision measurement of temperature differences with matched sensor pairs. A variety of dimensions offers flexible application possibilities.

## Features and specifications

Thermometer

**Measuring principle**

Resistance Temperature Detector

---

**Thermometer****Characteristic / Application**

metric style  
modular temperature assembly (paired)  
threaded process connection  
with neck  
incl. thermowell / protection tube  
(metal)

---

**Thermowell / protection tube**

welded protection tube

---

**Insert / probe**

mineral insulated (MI), flexible

---

**Outer diameter protection tube / Insert**

9,0 mm (0,35")

---

**Max. immersion length on request**

up to 4.000,00 mm (157,48")

---

**Material protection tube/ thermowell**

1.4571 (316Ti)

---

**Optional coating**

Not defined

---

**Process connection**

male thread:  
G1/2"

---

**Tip shape**

straight  
tapered

---

**Surface roughness Ra**

Not defined

---

## Thermometer

**Operating temperature range**

PT 100:

-50 °C ...200 °C

(-58 °F ...392 °F)

---

**Max. process pressure (static)**at 20 °C: 50 bar (725 psi)

---

**Accuracy**+/- 0.05 K (referring to delta-T)

---

**Response time**

depending on configuration

t50 = 10 s

t90 = 31 s

---

**Integration head transmitter**no

---

More information [www.au.endress.com/TST90](http://www.au.endress.com/TST90)