

Ultrasonic measurement Time-of-Flight Prosonic FDU91

Ultrasonic sensor for level and flow measurement for connection to FMU9x (measuring range up to 10m)



Benefits:

- Integrated temperature sensor for Time-of-Flight correction. Accurate measurements are possible, even if temperature changes are present
- Hermetically welded PVDF sensor for highest chemical resistance
- Suited for rough ambient conditions thanks to separate installation from the transmitter (up to 300m)
- Reduced build-up formation because of the self-cleaning effect
- Integrated automatic sensor detection for transmitters FMU90/ FMU95 for simple commissioning
- Weather resistant and flood-proof (IP 68)
- Integrated heating against a build-up of ice at the sensor (optional) ensures reliable measurement

More information and current pricing:

www.au.endress.com/FDU91

Specs at a glance

- **Process temperature** -40 °C ... 80 °C (-40 °F ... 176 °F)
- **Process pressure absolute / max. overpressure limit** 0.7 bar ... 4 bar abs (10 psi ... 58 psi)
- **Max. measurement distance** 5 m (16ft)
- **Accuracy** +/- 2mm + 0.17% of measured distance
- **Main wetted parts** PVDF (fully welded IP68 / NEMA 6P)

Field of application: The FDU91 ultrasonic sensor for continuous, non-contact and maintenance-free level measurement of fluids, pastes, sludges and powdery to coarse bulk materials. But also for flow measurement in open channels and measuring weirs. The measurement is unaffected by dielectric constant, density or humidity and also

unaffected by build-up due to the self-cleaning effect of sensors. Suited for explosion hazardous areas. Maximum measuring range in liquids 10m (33ft), solids 5m (16ft).

Features and specifications

Continuous / Solids

Measuring principle

Ultrasonic

Characteristic / Application

Separated version with field housing or top hat rail housing for control cabinet instrumentation, 300m in-between sensor and transmitter

Supply / Communication

4-wire (HART , Profibus DP)

Accuracy

+/- 2mm + 0.17% of measured distance

Ambient temperature

-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process temperature

-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process pressure absolute / max. overpressure limit

0.7 bar ... 4 bar abs
(10 psi ... 58 psi)

Main wetted parts

PVDF (fully welded IP68 / NEMA 6P)

Process connection

G / NPT 1"

Blocking distance

0.3 m (1 ft)

Continuous / Solids

Max. measurement distance5 m (16ft)

Communication

Transmitter:

4 ... 20 mA HART

Profibus DP

Certificates / ApprovalsATEX, FM, CSA, IEC Ex, JPN Ex, INMETRO, NEPSI, EAC Ex

OptionsSecond 4...20mA output

Components

Transmitter:

FMU90

Liquids

Measuring principleUltrasonic

Product headline

Version with separate transmitter in field housing or top hat rail housing
Cost effective solution for open channel flow measurement in water /
wastewater plants

Max. measurement error

accuracy:

distance measurement: +/- 2mm + 0.17%

resolution:

distance measurement: 1mm

Measuring rangemax measuring distance up to 10m / 32ft

Max. process pressureatm.

Liquids

Medium temperature range

-40...80°C
(-40...176°F)

Degree of protection

IP68

Display/Operation

Transmitter

Outputs

Transmitter:
4...20mA HART
Option: second 4...20mA output

Inputs

Transmitter

Digital communication

HART, PROFIBUS DP

Hazardous area approvals

ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

Continuous / Liquids

Measuring principle

Ultrasonic

Characteristic / Application

Separated version with field housing or top hat rail housing for control cabinet instrumentation, 300 m in-between sensor and transmitter

Supply / Communication

4-wire (HART, Profibus DP)

Accuracy

+/- 2 mm + 0.17% of measured distance

Continuous / Liquids**Ambient temperature**

-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process temperature

-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process pressure absolute / max. overpressure limit

0.7 bar ... 4 bar abs
(10 psi ... 58 psi)

Main wetted parts

PVDF (fully welded IP68 / NEMA6P)

Process connection

G / NPT 1"

Blocking distance

0.3 m (1 ft)

Application

Application

Max. measurement distance

Max. measurement distance

Communication

Transmitter:
4 ... 20 mA HART
Profibus DP

Certificates / Approvals

ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

Options

Second 4...20 mA output

Continuous / Liquids

Components

Transmitter:
FMU90, FMU95

Application limits

Application limits

More information www.au.endress.com/FDU91