

iTEMP TMT82 HART® 7 temperature transmitter

Dual channel, SIL compliant temperature transmitter for use in hazardous areas



More information and current pricing:

www.au.endress.com/TMT82

Benefits:

- Robust temperature transmitter delivering precise, long-term stable measurements for high plant availability
- SIL certification up to SIL2, SC3 according to IEC 61508:2010
- Versatile mounting and housing options: terminal head form B, DIN rail, field housing with separate terminal compartment, integrated display (**TID10**)
- Transmitter-sensor matching for highest measurement accuracy
- Sensor and hardware failure detection; diagnostic status information according to NAMUR NE 107
- Time-saving installation: Tool-free wiring with push-in terminal technology

Specs at a glance

- **Accuracy** (Pt100) $\leq 0,1K$ (digital) + 0,03% (set range)

Field of application: The iTEMP TMT82 is a highly reliable, accurate and long-term stable temperature transmitter for industrial processes requiring high availability. The versatile 2-channel device converts universal sensor inputs such as thermocouples or RTD into stable, scalable 4 to 20 mA output signals and **HART**® communication. With its built-in smart sensor monitoring capability and diagnostic status information according to NAMUR NE 107, the **SIL** 2, SC3 certified transmitter increases process safety and uptime.

Features and specifications

Temperature transmitters**Measuring principle**Head transmitter

Input2 x RTD, TC

Output1 x analog 4...20 mA / HART

Auxiliary power supply11...42 V DC

CommunicationHART-protocol

InstallationTerminal head form B, DIN-Rail housing or field mount housing

Accuracy(Pt100) $\leq 0,1K$ (digital) + 0,03% (set range)

Galvanic isolationyes

Temperature transmitters

Certification

Non-hazardous area

ATEX

CSA

FM

EAC

IECEX

NEPSI

FM+CSA

More information www.au.endress.com/TMT82