

# TA560

## Barstock thermowell

Made of drilled barstock material. Mainly used in heavy duty or general purpose applications.



More information and current pricing:

[www.au.endress.com/TA560](http://www.au.endress.com/TA560)

### Benefits:

- The extension and the immersion lengths as well as the bar dimensions can be chosen according to process requirements
- A wide choice of standard diameters and materials is available; other versions can be ordered according to specification
- Different grades of surface finishing are also available
- The process connection is threaded. The thermowell stem shape can be straight or conical

### Specs at a glance

- **Max. process pressure (static)** 500 bar (7252 psi)
- **Maximum standard immersion length** 900 mm (35,43")
- **Max. immersion length on request** 5.000 mm (196,85")

**Field of application:** Due to the challenging process conditions by heavy duty applications the load capacity of a thermowell must be calculated exactly. Dye penetration tests, ultrasound test, helium leakage test, pressure endurance test as well as various, non-destructive material tests prove the quality of materials and processing.

## Features and specifications

Thermowell

### Measuring principle

Bar stock Thermowell

## Thermowell

**Characteristic / Application**

metric style

threaded process connection

hexagonal extension

**Head connection**

internal thread:

1/2" NPT

**Maximum standard immersion****length**

900 mm (35,43")

**Max. immersion length on request**

5.000 mm (196,85")

**Process connection**

thread:

3/4" NPT

**Thermowell root diameter**

20 mm (0,79")

22 mm (0,87")

**Medium contact material**

1.4401 (316)

1.4404 (316L)

1.4571 (316Ti)

## Thermowell

**Wetted part finishing (Ra)**< 0,8  $\mu\text{m}$  (31,50  $\mu\text{in}$ )< 1,6  $\mu\text{m}$  (63,00  $\mu\text{in}$ )**Tip shape**

straight

conical

**Temperature range**-200...700  $^{\circ}\text{C}$  (-328...1.292  $^{\circ}\text{F}$ )**Max. process pressure (static)**

500 bar (7252 psi)

**Max. process pressure at 400  $^{\circ}\text{C}$** 

300 bar (4351 psi)

More information [www.au.endress.com/TA560](http://www.au.endress.com/TA560)