

# Stamolys CA71COD



More information and current pricing:

[www.au.endress.com/CA71COD](http://www.au.endress.com/CA71COD)

## Benefits:

- Reliable correlation to DIN and GB laboratory COD methods
- Cost and time savings by replacing manual cuvette tests
- Minimal contact by personnel with harmful substances increases operational safety
- Convenient online documentation of COD load curves
- Robust: Optional backflush pump and stirred sample vessel

## Specs at a glance

- **Measurement range** 0 ... 200 mg/l O<sub>2</sub> 50 ... 5000 mg/l O<sub>2</sub>
- **Process temperature** 5°C ... 40°C 40 ... 100°F
- **Process pressure** pressureless

**Field of application:** The CA71COD online analyzer actively supports your maintenance strategy by replacing manual cuvette tests. The constant monitoring of the chemical oxygen demand (COD) increases process safety and supports a load-based billing system for industrial wastewater treatment plants. An optional backflush pump provides reliable measurement even in inlet wastewater applications. The analyzer waste is split into dichromate and dichromate-free and ensures high environmental compliance.

## Features and specifications

### Analyser

#### Measuring principle

Colorimetric

#### Characteristic

Analyzer for the chemical oxygen demand  
Dichromat method

---

**Analyser****Size**

648 x 436 x 250 mm  
25.27 x 17.00 x 9.75 inch

---

**Design**

GRP

---

**Process temperature**

5°C ... 40°C  
40 ... 100°F

---

**Ambient temperature**

10°C ... 35°C  
50 ... 95°F

---

**Process pressure**

pressureless

---

**Sample flow rate**

min. 5ml/min

---

**Consistency of the sample**

watery and homogenized

---

**Specials**

Chloride removal without Hg  
variable decomposition times

---

**Application**

Wastewater / Processwater

---

**Power supply**

230 V AC, 50 Hz  
230V AC 60 Hz

---

**Output / communication**

0/4 ... 20 mA  
Contacts: 2 limit contacts (per channel), 1 system alarm  
contact

---

## Analyser

### Measurement range

0 ... 200 mg/l O<sub>2</sub>

50 ... 5000 mg/l O<sub>2</sub>

---

### Consumables

Chemicals necessary

---

More information [www.au.endress.com/CA71COD](http://www.au.endress.com/CA71COD)