

# Picomag electromagnetic flowmeter

Smart magmeter for utilities – intuitive ·  
convenient · multivariable



## Benefits:

- Time-saving, easy configuration even in places difficult to reach – secure Bluetooth connection
- Fewer measuring points necessary – simultaneous flow, conductivity and temperature measurement
- Cost-efficient specialist for use in tight spaces e.g. skids – sensor and transmitter in one housing
- Quick offline configuration check – unique, comfortable knock functionality
- Simple device access through its whole lifecycle – no manual needed due to intuitive SmartBlue App
- Instant local process monitoring – large, user-friendly display of all measurement activities
- Flexible integration into all fieldbus systems – plug-and-play device with IO-Link

from **A\$918.00**

Price as of 30.11.2022

More information and current pricing:

[www.au.endress.com/DMA](http://www.au.endress.com/DMA)

## Specs at a glance

- **Max. measurement error** Volume flow: +/-0.8% o.r. +/- 0.1% o.f.s
- **Measuring range** up to 750 l/min
- **Medium temperature range** -10 to 70°C (+14 to +158 °F)  
Permissible short-term temperature, maximum one hour: 85 °C (185 °F) Repetition after 4 hours at the earliest
- **Max. process pressure** 16 bar
- **Wetted materials** PEEK, Stainless Steel, FKM, EPDM Electrodes: 1.4404/316L

**Field of application:** Picomag is the economical magmeter for many applications in secondary circuits with conductive liquids in all industries.

End customers, skid builders, equipment manufacturers and system integrators value the space-saving Picomag for its flexible installation capabilities. Additionally, its future-oriented, intuitive operation via SmartBlue app on every Bluetooth-enabled smartphone or tablet ensures fast, secure and simple commissioning.

## Features and specifications

### Liquids

#### Measuring principle

Electromagnetic

#### Product headline

Smart magmeter for utilities – intuitive · convenient · multivariable. Time-saving, easy configuration even in places difficult to reach – secure Bluetooth connection. Ideal for process quality control and monitoring due to temperature and conductivity measurement in utilities.

#### Sensor features

Fewer measuring points necessary – simultaneous flow, conductivity and temperature measurement. Cost-efficient specialist for use in tight spaces e.g. skids – sensor and transmitter in one housing. High shock and vibration resistance. Degree of protection: IP65/67. Empty pipe detection.

#### Transmitter features

Quick offline configuration check – unique, comfortable knock functionality. Simple device access through its whole lifecycle – no manual needed due to intuitive SmartBlue app. Effortless configuration of several devices – settings can be saved and loaded into other meters. Flexible integration into all fieldbus systems – plug-and-play device with IO-Link. Wireless remote access via Bluetooth SmartBlue app. IO-Link and various I/Os for all line-sizes. 1.4" TFT color display with backlight.

#### Nominal diameter range

DN15 to 50 (1/2 to 2")

---

## Liquids

**Wetted materials**

PEEK, Stainless Steel, FKM, EPDM  
Electrodes: 1.4404/316L

---

**Measured variables**

Volume flow, Temperature, Conductivity

---

**Max. measurement error**

Volume flow: +/-0.8% o.r. +/- 0.1% o.f.s

---

**Measuring range**

up to 750 l/min

---

**Max. process pressure**

16 bar

---

**Medium temperature range**

-10 to 70°C (+14 to +158 °F)

Permissible short-term temperature, maximum one hour:

85 °C (185 °F)

Repetition after 4 hours at the earliest

---

**Ambient temperature range**

-10 to 60 °C

---

**Sensor housing material**

1.4404/316L, Polycarbonate

---

**Transmitter housing material**

1.4404/316L, Polycarbonate

---

**Degree of protection**

IP 65/67

---

**Display/Operation**

Integrated display, operation via SmartBlue app

---

## Liquids

### Outputs

Current (4 to 20mA)

Pulse

Switch

Voltage (2 to 10V)

---

### Inputs

Status

---

### Digital communication

IO-Link

---

### Power supply

18 to 30V DC

---

### Product safety

cULus listing

---

### Hygienic approvals and certificates

Drinking water approvals: NSF

---

More information [www.au.endress.com/DMA](http://www.au.endress.com/DMA)