

Thermocouple TMT142C



More information and current pricing:

www.be.endress.com/TMT142C

Benefits:

- Dual compartment housing
- Backlit display with large measured value, bar graph and fault condition indication
- Galvanic isolation 2 kV (sensor input to the output)
- Wide range of threaded thermowell connections available as standard
- Replaceable measuring insert comprising a mineral insulated tube (SS 316L/1.4404)
- Approvals for hazardous areas: Flameproof enclosure (Ex d), Intrinsic safety (Ex ia), Non-sparking (Ex nA)
- Aluminum or stainless steel housing, degree of protection IP67, NEMA 4x

Specs at a glance

- **Accuracy** class 1 acc. to IEC 60584 class 2 acc. to IEC 60584
- **Response time** depending on configuration $t_{50} = 3 \text{ s}$ $t_{90} = 7 \text{ s}$
- **Max. process pressure (static)** depending on thermowell
- **Operating temperature range** Type K: $-40 \text{ °C} \dots 800 \text{ °C}$ ($-40 \text{ °F} \dots 1.472 \text{ °F}$) Type J: $-40 \text{ °C} \dots 750 \text{ °C}$ ($-40 \text{ °F} \dots 1.382 \text{ °F}$)
- **Max. immersion length on request** up to 30.000,00 mm (1.181,10")

Field of application: The robust thermometer is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas and Energy industry. The thermometer fulfills the corresponding safety requirements due to various certificates and tests. The use of a transmitter leads to higher accuracy and reliability in comparison to directly wired sensors.

Features and specifications

Thermometer

Measuring principle

Thermocouple

Characteristic / Application

US style
 modular temperature assembly
 for heavy duty applications
 suitable for hazardous areas
 threaded process connection
 to use with thermowell
 backlit display

Thermowell / protection tube

to use with thermowell

Insert / probe

mineral insulated (MI), flexible

Outer diameter protection tube / Insert

Not defined

Max. immersion length on request

up to 30.000,00 mm (1.181,10")

Material protection tube/ thermowell

Not defined

Optional coating

Not defined

Process connection

male thread:

G1/2"

NPT1/2"

NPT3/4"

union nut:

NPT1/2"

M24x1.5

Thermometer

Tip shape

straight

Operating temperature range

Type K:

-40 °C ...800 °C

(-40 °F ...1.472 °F)

Type J:

-40 °C ... 750 °C

(-40 °F ...1.382 °F)

Max. process pressure (static)

depending on thermowell

Accuracy

class 1 acc. to IEC 60584

class 2 acc. to IEC 60584

Response time

depending on configuration

t₅₀ = 3 st₉₀ = 7 s**Integration head transmitter**yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)**Ex - approvals**

ATEX II

Explosion proof

More information www.be.endress.com/TMT142C