

iTHERM ModuLine TT151

Bar stock thermowell for a wide range of heavy duty industrial applications



More information and current pricing:

www.be.endress.com/TT151

Benefits:

- TT151 is an industry standard thermowell manufactured from round barstock
- Modular configuration according to DIN 43772 or ASME B40.9 or more flexible as universal version
- Extension, immersion length and total length can be chosen according to process requirements
- Wide range of dimensions, materials and process connections available

Specs at a glance

- **Max. process pressure (static)** 500 bar (7252 psi) Depending on Configuration
- **Maximum standard immersion length** 1500 mm

Field of application: The thermowell design is based on DIN43772 or ASME B40.9 and additionally it is available as a universal version that can be configured flexibly. The thermowell guarantees a good resistance to typical industrial processes. It comprises a full material bar stock with a root diameter from 9 to 50 mm. The tip can be straight, tapered or stepped. The thermowell can be fitted to a pipe or vessel in the system using a selection of commonly used flanged process connection, thread or weld-in versions.

Features and specifications

Thermowell

Measuring principle

Bar stock Thermowell

Thermowell

Characteristic / Application

metric style

compliant according to ASME or DIN

standard

universal use

Head connection

internal thread:

M14x1,5

M18x1,5

M20x1,5

M27x1,5

1/2" NPT

1/2" NPSM

1/2" NPSC

G1/2"

G2/3"

Maximum standard immersion length

1500 mm

Process connection

To be

threaded

weld in

with flange according to ASME or EN or ISO

Thermowell**Thermowell root diameter**

9...50 mm

Medium contact material

Wide selection of materials including:

316

316L

316Ti

347

310

Alloy600

AlloyC276

10CrMo9-10

13CrMo4-5

16Mo3

A105

C22.8

Duplex

Titan Gr.2

Thermowell

Wetted part finishing (Ra)< 0.8 μm (31.50 μin)< 1.6 μm (63.00 μin)

DIN Standard

Tip shape

Straight

Tapered

Stepped

partly tapered

Temperature range-200...1100 $^{\circ}\text{C}$ (-328...2.012 $^{\circ}\text{F}$)

Depending on Configuration

Max. process pressure (static)

500 bar (7252 psi)

Depending on Configuration

Max. process pressure at 400 $^{\circ}\text{C}$

depends on process connection and material

More information www.be.endress.com/TT151