

iTHERM TT411

Protection tube

Designed for hygienic and aseptic applications in the Food & Beverages and Life Sciences industries



More information and current pricing:

www.be.endress.com/TT411

Benefits:

- iTHERM QuickNeck – cost and time savings thanks to simple, tool-free recalibration of the insert used
- Over 50 hygienic process connections
- Global portfolio with metric and imperial versions
- International certification: hygiene standards as per 3-A®, EHEDG, ASME BPE, FDA, TSE Certificate of Suitability
- Optional: 1.4435 material, delta ferrite content < 1%
- Fast response time owing to reduced tips with thin walls
- State of the art Tee and Elbow elements, without welds and dead legs and with best in class hygienic design

Specs at a glance

- **Max. process pressure (static)** 40 bar (580 psi)
- **Maximum standard immersion length** 4.000 mm (157,48")
- **Max. immersion length on request** Not defined

Field of application: Best applicable for use in hygienic or aseptic pipes and containers or tanks even with very small immersion lengths. It meets increased protection requirements of the temperature sensor regarding physical and chemical effects. Ideally suited to all measuring points that require regular recalibration by simply replacing the insert in closed processes.

Features and specifications

Thermowell

Measuring principle

Fabricated Thermowell

Characteristic / Application

metric style

hygienic/aseptic design (3-A[®], EHEDG, ASME BPE, FDA)

hygienic process connections

QuickNeck for easy and cost saving recalibration

Head connection

QuickNeck

male thread:

M24x1,5

G3/8"

Maximum standard immersion length

4.000 mm (157,48")

Max. immersion length on request

Not defined

Process connection

compression fitting

weld in adaptor

clamp connections acc. to ISO2852

screwed pipe joint acc. to DIN 11851

aseptic screwed pipe joint acc. to DIN 11864-1

metallic sealing system

thread acc. to ISO 228 for liquiphant adaptor APV Inline

Varivent

Ingold

SMS 1147

Neumo Biocontrol

Tee and elbow thermowells DIN11865

Thermowell**Thermowell root diameter**

6,0 mm (0,24")

9,0 mm (0,35")

12,7 mm (0,5")

Medium contact material

1.4435 delta-ferrit < 1%

316L

Wetted part finishing (Ra)

< 0,76 µm (29,92 µin)

< 0,38 µm (14,96 µin)

< 0,38 µm (14,96 µin) electropolished

Tip shape

straight

reduced

tapered

Temperature range-200...650 °C (-328...1.202 °F)

Max. process pressure (static)40 bar (580 psi)

Max. process pressure at 400 °Cdepends on process connection

More information www.be.endress.com/TT411