

Trilvorkniveaudetectie Liquiphant FTL51

Niveauschakelaar met verlengbuis voor vloeistoffen in alle sectoren



Meer informatie en actuele prijzen:

www.be.endress.com/FTL51

Voordelen:

- Gebruik in veiligheidssystemen die functionele veiligheid SIL2/SIL3 vereisen volgens IEC 61508/IEC 61511-1
- Internationale certificaten voor explosieveiligheid en overvulbeveiliging (WHG)
- Geen kalibratie nodig, eenvoudig op te starten
- Geen mechanisch bewegende delen: geen onderhoud, geen slijtage, lange levensduur.
Vork wordt op beschadiging gecontroleerd: gegarandeerde werking
- Second line of defense ter bescherming van het milieu
- Diverse gestandaardiseerde procesaansluitingen voor alle toepassingen
- Sensor is gemaakt van roestvrij staal (316L) en een zeer corrosiebestendig materiaal (legering)

Overzicht specificaties

- **Process temperature** -50 °C...+150 °C (-58 °F...+302 °F)
- **Process pressure absolute / max. overpressure limit**
Vacuum...100 bar
- **Min. density of medium** 0.5g/cm³(0.4g/cm³ optional)

Toepassingsgebied: De Liquiphant FTL51 is een niveauschakelaar met een verlengbuis voor gebruik in gevaarlijke gebieden en beschikt over alle internationale certificaten. Te gebruiken in alle industrieën. De FTL51 biedt functionele veiligheid SIL2/SIL3. De second line of defense garandeert de hoogste mate van veiligheid en beschikbaarheid van het instrument. Betrouwbare meetwaarden, niet beïnvloed door:

veranderende media-eigenschappen, stroming, turbulentie, gasbellen, schuim, trillingen of aangroei.

Kenmerken en specificaties

Density

Meetprincipe

Vibration Density

Characteristic / Application

Liquiphant M Density
with Density Computer FML621
Temperature and pressure measurement
Modular housing concept
Wide range of process connections
Pipe extension up to 3 m (6 m option)

Supply / Communication

Transmitter power supply (MUS)

Ambient temperature

-50...70°C
-50...60°C for hazardous applications

Process temperature

0...80°C (validity of accuracy data)
-50...0°C / 80...150 °C (with reduced technical data)

Process pressure absolute

0...25 bar
>25..100 bar (with reduced technical data)

Wetted parts

316L/C4

Sensor length

115...3000 mm
>3000...6000 mm (Option)

Density

Output

Pulse

Certificates / Approvals

ATEX, FM, CSA C/US, IEC Ex, TIIS, INMETRO, NEPSI

Specialities

Commissioning with ReadWin2000

Components

Density Computer FML621

Other approvals and certificates

SIL2/ SIL3

Point Level / Liquids

Meetprinciple

Vibration Liquids

Characteristic / Application

Modular housing concept

wide range of process connections

Analogue and bus interfaces

Extensive certificate range (e.g. Ex, WHG)

pipe extension up to 3m (6m option)

Specialities

Foam detection

Detect a density change

second line of defense

Point Level / Liquids**Supply / Communication**

PROFIBUS PA
19...253V AC
10...55V DC-PNP
19...253V AC or 10...55V DC
8/16mA, 11...36V DC
NAMUR
PFM

Ambient temperature

-50 °C...+70 °C
(-58 °F...+158 °F)

Process temperature

-50 °C...+150 °C
(-58 °F...+302 °F)

Process pressure absolute / max. overpressure limit

Vacuum...100 bar

Min. density of medium

0.5g/cm³(0.4g/cm³ optional)

Main wetted parts

316L / Alloy

Process connection

Thread:
G3/4A, G1A, R3/4", R1, NPT3/4, NPT1
Flange:
DN25...DN100,
ASME 1"...4",
JIS 25A...100A

Process connection hygienic

Tri-Clamp ISO2852

Point Level / Liquids**Sensor length**

Length 130mm (5.12") (Liquiphant II)
148mm...6000mm (5.83"...236")

Communication

PROFIBUS PA
19...253V AC
10...55V DC-PNP
19...253V AC bzw 10...55V DC
8/16mA, 11...36V DC
NAMUR
PFM

Certificates / Approvals

ATEX, FM, CSA C/US, IEC Ex, TIIS, INMETRO, NEPSI

Safety approvals

SIL2/ SIL3

Design approvals

EN 10204-3.1
NACE MR0175, MR0103
ASME B31.3
AD2000

Marine approval

GL/ ABS/ DNV

Options

Heavy duty stainless steel housing mainly for the oil and gas industry

Components

FTL325P/FTL375P Interface PFM
FTL325N/FTL375N Interface NAMUR

Successor

Liquiphant FTL51B

Meer informatie www.be.endress.com/FTL51