

8-kanaals transmitter Liquiline CM448

Flexibel multiparameter-procesinstrument voor alle industrieën



Meer informatie en actuele prijzen:

www.be.endress.com/CM448

Voordelen:

- **Slimme eenvoud:**
één controller voor alle parameters en toepassingen, intuïtieve gebruikersinterface, automatische sensorherkenning, hot plug & play met vooraf gekalibreerde Memosens-sensoren.
- **Compleet pakket:**
8 kanalen in één instrument zorgen voor een hoge flexibiliteit en maken het instrument geschikt voor elke meettaak.
- **Naadloze systeemintegratie:**
de unieke set communicatiestandaarden is geschikt voor elk distributed control system (DCS).
- **Eenvoudige en veilige inbedrijfstelling:**
door de configuratie op een SD-kaart op te slaan kunnen de instellingen snel naar een tweede installatie worden gekopieerd.
- **Procesbewaking op afstand:**
geïntegreerde webserver die de operator in staat stelt om op afstand diagnosegegevens te bekijken, configuraties uit te voeren of toegang te krijgen tot instrumentparameters in elke webbrowser - zelfs via smartphone.
- **Hogere beschikbaarheid, lagere kosten:**
Heartbeat Technology maakt statusgericht onderhoud en eenvoudige verificatie van het gehele meetpunt mogelijk en helpt bij het uitvoeren van optimalisatiemaatregelen.

Overzicht specificaties

- **Input** 1 to 8x Memosens digital input 2x 0/4 to 20mA Input optional 2 to 4x Digital input optional

Output / communication 2 to 8x 0/4 to 20 mA current outputs, alarmrelay 4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

- **Ingres protection** IP66 / IP67

Toepassingsgebied: De Liquiline CM448 is een digitale multiparameter-transmitter voor procesbewaking en -besturing en is geschikt voor alle toepassingen. De 8-kanaals controller bespaart u tijd en geld door een naadloze systeemintegratie, een eenvoudige bediening en een verminderde behoefte aan reserveonderdelen. Pas de controller volledig aan uw meettaak aan en sluit 1 tot 8 sensoren aan. De Liquiline CM448 biedt u alle voordelen van een best-in-class transmitter, van slimme eenvoud tot optimale procesveiligheid.

Kenmerken en specificaties

Analyser

Meetprincipe

Potentiometric / ISE

Characteristic

Robust plastic housing
All non-ex applications

Process temperature

-20 to 55 °C (0 to 130 °F)

Application

Modular 4 wire controller
Multichannel: 1 to 8 digital channels for Memosens protocol
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity
8 sensors connectable in any combination
Functionality modular extendable at any time
Plug and play for modules and sensors

Analyser

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Input

1 to 8x Memosens digital input
2x 0/4 to 20mA Input optional
2 to 4x Digital input optional

Disinfection

Meetprincipe

Free chlorine

Application

Modular 4 wire controller
Multichannel: 1 to 8 digital channels for Memosens protocol
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity
8 sensors connectable in any combination
Functionality modular extendable at any time
Plug and play for modules and sensors

Characteristic

Robust plastic housing
All non-ex applications

Design

8x Memosens input, 2 to 8x current output,
Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

Material

Housing base: PC-FR
Housing seal EPDM

Dimension

237 x 194 x 162 mm
9.33 x 7.64 x 6.38 inch

Disinfection

Process temperature

-20 to 55 °C (0 to 130 °F)

Input

1 to 8x Memosens digital input
2x 0/4 to 20mA Input optional
2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

ORP / Redox

Meetprincipe

Sensor ORP / Redox

Application

Modular 4 wire controller
Multichannel: 1 to 8 digital channels for Memosens protocol
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity
8 sensors connectable in any combination
Functionality modular extendable at any time
Plug and play for modules and sensors

Characteristic

Robust plastic housing
All non-ex applications

Design

8x Memosens input, 2 to 8x current output,
Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

ORP / Redox

Material

Housing base: PC-FR

Housing seal EPDM

Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

Process temperature

-20 to 55 °C (0 to 130 °F)

Ingres protection

IP66 / IP67

Input

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Oxygen

Meetprincipe

Amperometric oxygen measurement

Application

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Oxygen

Characteristic

Robust plastic housing
All non-ex applications

Design

8x Memosens input, 2 to 8x current output,
Alarmrelay, 2x relay, SD card for software update and copy & paste of
setup

Material

Housing base: PC-FR
Housing seal EPDM

Dimension

237 x 194 x 162 mm
9.33 x 7.64 x 6.38 inch

Process temperature

-20 to 55 °C (0 to 130 °F)

Input

1 to 8x Memosens digital input
2x 0/4 to 20mA Input optional
2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Turbidity

Meetprincipe

Single beam scattered light

Turbidity

Application

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

8x Memosens input, 2 to 8x current output,

Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

Material

Housing base: PC-FR

Housing seal EPDM

Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

Process temperature

-20 to 55 °C (0 to 130 °F)

Ingres protection

IP66 / IP67

Input

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Turbidity

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Conductivity

Meetprincipe

Potentiometric

Application

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive,
dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

8x Memosens input, 2 to 8x current output,

Alarmrelay, 2x relay, SD card for software update and copy & paste of
setup

Material

Housing base: PC-FR

Housing seal EPDM

Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

Conductivity

Ingres protection

IP66 / IP67

Input

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

pH

Meetprincipe

Potentiometric

Application

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

8x Memosens input, 2 to 8x current output,

Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

pH

Material

Housing base: PC-FR

Housing seal EPDM

Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

Process temperature

-20 to 55 °C (0 to 130 °F)

Ingres protection

IP66 / IP67

Input

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Meer informatie www.be.endress.com/CM448