

TA556

Barstock thermowell

Made of drilled barstock material. Mainly used in heavy duty or general purpose applications.



Meer informatie en actuele prijzen:

www.be.endress.com/TA556

Voordelen:

- The extension and the immersion lengths as well as the bar dimensions can be chosen according to process requirements
- A wide choice of standard materials and process connections is available; other versions can be ordered according to specification
- Different grades of surface finishing are also available
- The thermowell stem shape is stepped
- The process connection can be threaded or flanged weld

Overzicht specificaties

- **Max. process pressure (static)** 500 bar (7252 psi)
- **Maximum standard immersion length** 900 mm (35,43")
- **Max. immersion length on request** 5.000 mm (196,85")

Toepassingsgebied: Due to the challenging process conditions by heavy duty applications the load capacity of a thermowell must be calculated exactly. Dye penetration tests, ultrasound test, helium leakage test, pressure endurance test as well as various, non-destructive material tests prove the quality of materials and processing.

Kenmerken en specificaties

Thermowell

Meetprincipe

Bar stock Thermowell

Thermowell

Characteristic / Application

metric style
various process connections
round extension

Head connection

internal thread:
3/4" NPT

Maximum standard immersion length

900 mm (35,43")

Max. immersion length on request

5.000 mm (196,85")

Process connection

thread:
1" NPT
flange:
ASME 1" 300 RF (B16.5)
ASME 1" 600 RF (B16.5)
ASME 1 1/2" 150 RF (B16.5)
ASME 1 1/2" 300 RF (B16.5)
ASME 1 1/2" 600 RF (B16.5)
ASME 1 1/2" 600 RTJ (B16.5)
ASME 2" 300 RF (B16.5)
ASME 2" 600 RF (B16.5)
ASME 2" 300 RTJ (B16.5)
ASME 2" 600 RTJ (B16.5)

Thermowell root diameter

25 mm (0,98")

Medium contact material

1.4401 (316)
1.4404 (316L)
1.4571 (316Ti)

Thermowell

Wetted part finishing (Ra)< 0.8 μm (31.50 μin)< 1.6 μm (63.00 μin)

Tip shape

straight

tapered

Temperature range-200...700 $^{\circ}\text{C}$ (-328...1.292 $^{\circ}\text{F}$)

Max. process pressure (static)500 bar (7252 psi)

Max. process pressure at 400 $^{\circ}\text{C}$ 300 bar (4351 psi)

Meer informatie www.be.endress.com/TA556