

Proline Promag H 300 elektromagnetische flowmeter

Specialist voor hygiënische toepassingen met een compacte, gemakkelijk toegankelijke transmitter



Meer informatie en actuele prijzen:

www.be.endress.com/5H3B

Voordelen:

- Flexibel installatieconcept – talrijke hygiënische procesaansluitingen
- Energiebesparende flowmeting – geen drukverlies door vernauwing van de doorsnede
- Onderhoudsvrij – geen bewegende onderdelen
- Volledige toegang tot proces- en diagnose-informatie – talrijke, vrij te combineren I/O's en veldbussen
- Verminderde complexiteit en verscheidenheid – vrij configureerbare I/O-functionaliteit
- Geïntegreerde verificatie – Heartbeat Technology

Overzicht specificaties

- **Max. measurement error** Volume flow (standard): $\pm 0.5\%$ o.r. ± 1 mm/s (0.04 in/s) Volume flow (option) $\pm 0.2\%$ o.r. ± 2 mm/s (0.08 in/s)
- **Measuring range** 0.06 dm³/min to 600 m³/h (0.015 gal/min to 2 650 gal/min)
- **Medium temperature range** -20 to +150 °C (-4 to +302 °F)
- **Max. process pressure** PN 40, Class 150, 20K
- **Wetted materials** Liner: PFA Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); Tantalum; Platinum Process Connections: stainless steel, 1.4404 (F316L); PVDF; PVC adhesive sleeve Seals: O-ring seal (EPDM, FKM, Kalrez), aseptic molded seal (EPDM, FKM, silicone) Grounding Rings: stainless steel, 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); tantalum

Toepassingsgebied: Promag H is de gewenste sensor voor hygiënische toepassingen met de hoogste eisen in de voedingsmiddelen- en drankindustrie en de life sciences-industrie. Met zijn compacte transmitter biedt de Promag H 300 een hoge flexibiliteit wat betreft bediening en systeemintegratie: toegang vanaf één zijde, weergave op afstand en verbeterde connectiviteitsopties. Heartbeat Technology waarborgt de compatibiliteit en de procesveiligheid.

Kenmerken en specificaties

Liquids

Meetprincipe

Electromagnetic

Product headline

Specialist for hygienic applications with a compact, easily accessible transmitter.

Dedicated to demanding applications in the food and beverage as well as in life sciences industries.

Sensor features

Flexible installation concept – numerous hygienic process connections.

Energy - saving flow measurement – no pressure loss due to cross section constriction. Maintenance - free – no moving parts.

Liner made of PFA. Sensor housing made of stainless steel (3-A, EHEDG).

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Wetted materials CIP, SIP cleanable. Compact hygienic dual-compartment housing with IP69 and up to 3 I/Os. Backlit display with touch control and WLAN access.

Nominal diameter range

DN 2 to 150 (1/12 to 6")

Liquids

Wetted materials

Liner: PFA

Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022);
Tantalum; Platinum

Process Connections: stainless steel, 1.4404 (F316L); PVDF; PVC
adhesive sleeve

Seals: O-ring seal (EPDM, FKM, Kalrez), aseptic molded seal (EPDM,
FKM, silicone)

Grounding Rings: stainless steel, 1.4435 (316L); Alloy C22, 2.4602
(UNS N06022); tantalum

Measured variables

Volume flow, temperature, conductivity, mass flow, corrected volume
flow, corrected conductivity

Max. measurement error

Volume flow (standard): $\pm 0.5\%$ o.r. ± 1 mm/s (0.04 in/s)

Volume flow (option) $\pm 0.2\%$ o.r. ± 2 mm/s (0.08 in/s)

Measuring range

0.06 dm³/min to 600 m³/h (0.015 gal/min to 2 650 gal/min)

Max. process pressure

PN 40, Class 150, 20K

Medium temperature range

-20 to +150 °C (-4 to +302 °F)

Ambient temperature range

-40 to +60 °C (-40 to +140 °F)

Sensor housing material

1.4301 (304), corrosion resistant

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; stainless steel for
hygenic transmitter design

Liquids

Degree of protection

IP66/67, type 4X enclosure
IP69

Display/Operation

4-line backlit display with touch control (operation from outside)
Configuration via local display and operating tools possible
Remote display available

Inputs

Status input
4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V
AC 100 to 230 V
AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, INMETRO, NEPSI, EAC

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)
Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Liquids

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

Sanitary approval: EHEDG, 3-A, liner and seals acc. to FDA, cGMP

Meer informatie www.be.endress.com/5H3B