

# Proline Prosonic Flow 93W ultrasone flowmeter

Instrument met automatische frequentiescan voor max. meetprestaties met een uitgebreid aantal uitgangen



Meer informatie en actuele prijzen:

[www.be.endress.com/93W](http://www.be.endress.com/93W)

## Voordelen:

- Lage investeringskosten – kostenefficiëntie neemt toe met pijpdiameter (tot DN 4000)
- Langdurig stabiel signaal - onderhoudsvrije permanente montage van buitenaf met koppelpads
- Procestransparantie – geschikt voor diagnose
- Maximale prestaties – uitgebreide functionaliteit en diagnose
- Flexibele gegevensoverdrachtopties – talrijke communicatietypen
- Automatisch herstel van gegevens voor onderhoud

## Overzicht specificaties

- **Max. meetfout** Volume flow:  $\pm 3\%$  o.r. for DN15  $\pm 2\%$  o.r. for DN25 to 200  $\pm 2\%$  o.r. above DN200
- **Measuring range** 0.3 to 10 m/s (1 to 33 ft/s)
- **Medium temperature range** Clamp-on:  $-20$  to  $+80$  °C ( $-4$  to  $+176$  °F) Insertion version:  $-40$  to  $+80$  °C
- **Max. process pressure** N/A
- **Wetted materials** Clamp on system: Sensor holder 1.4308/CF-8  
Sensor housing 1.4301/304 Strapping bands 1.4301/304

**Toepassingsgebied:** De Prosonic Flow W clamp-on-sensor is speciaal ontworpen voor water- en afvalwatertoepassingen. In combinatie met de Prosonic Flow 93-transmitter met aanraakbediening, 4-regelig display en uitgebreide functionaliteit biedt de Prosonic Flow 93W hoge nauwkeurigheid in standaardtoepassingen in de waterindustrie.

## Kenmerken en specificaties

## Liquids

### Meetprincipe

Ultrasonic flow

---

### Product headline

Device with automatic frequency scan for max. measuring performance with a wide range of outputs.

Clamp-on flow measurement of process water, salt water, demineralized water, drinking & wastewater.

---

### Sensor features

Low capital investment – cost-effectiveness increases with pipe diameter (up to DN 4000/156"). Long-term stable signal – maintenance-free permanent mounting from outside with coupling pads. Process transparency – diagnostic capability.

Medium temperature: -20 to +80 °C (-4 to +176 °F). Degree of protection IP68 (Type 6P enclosure) for pipes under water. Shock and vibration resistance according to IEC 68-2-6.

---

### Transmitter features

Highest performance – extended functionality and diagnostics. Flexible data transfer options – numerous communication types. Automatic recovery of data for servicing.

Aluminium transmitter housing. 4 - line backlit display with touch control. HART, PROFIBUS PA/DP, FOUNDATION Fieldbus.

---

### Nominal diameter range

Single channel, 1 or 2 paths : DN15 to 4000 (1/2 to 160")

Dual channel, 1 or 2 paths : DN15 to 4000 (1/2 to 160")

---

### Wetted materials

Clamp on system:

Sensor holder 1.4308/CF-8

Sensor housing 1.4301/304

Strapping bands 1.4301/304

---

### Measured variables

Volume flow channel 1&2, average volume flow, volume flow difference, sound velocity, flow velocity, totalizer

---

---

**Liquids****Max. meetfout**

Volume flow:

±3% o.r. for DN15

±2% o.r. for DN25 to 200

±2% o.r. above DN200

---

**Measuring range**

0.3 to 10 m/s (1 to 33 ft/s)

---

**Max. process pressure**

N/A

---

**Medium temperature range**

Clamp-on: -20 to +80 °C (-4 to +176 °F)

Insertion version: -40 to +80 °C

---

**Ambient temperature range**

-20 to +60 °C (-4 to +140 °F)

---

**Sensor housing material**

N/A

---

**Transmitter housing material**

Wall-mounted housing: powder-coated die-cast aluminum

---

**Degree of protection**

IP67, type 4X for transmitter, IP68 (option)

IP67 type 4X for sensors

IP68 type 6P for sensors (option). Transmitter: IP67, type 4X enclosure

---

**Display/Operation**

4 lines backlit display with three optical keys

---

**Outputs**

1x 4-20 mA HART

1x Pulse/frequency/switch output (passive)

---

**Inputs**

N/A

## Liquids

### Digital communication

HART, PROFIBUS PA, PROFIBUS DP, FOUNDATION Fieldbus

---

### Power supply

AC 85 to 260 V

AC 20 to 55 V

DC 16 to 62 V

---

### Hazardous area approvals

ATEX, FM, CSA

---

### Other approvals and certificates

Flowmeter verification for DN15, 25, 40, 50, 100, 250, 400 only

Marine certificate

EAC marking

---

### Product safety

CE, C-Tick, EAC marking

---

### Metrological approvals and certificates

Flowmeter verification for DN15, 25, 40, 50, 100, 250, 400 only

---

### Marine approvals and certificates

Marine certificate

---

Meer informatie [www.be.endress.com/93W](http://www.be.endress.com/93W)