

Absolute and gauge pressure Ceraphant PTP31B

Cost-effective pressure switch with welded metal sensor for measurement in gases, steams or liquids



Benefícios:

- Integrated switching electronics for decentral and economic process monitoring and control
- Function check and information on-site thanks to LEDs and digital display
- Overload-resistant sensor up to 400bar
- Small flush mounted process connections
- IO-Link reduces costs and complexity due to easy configuration and flexible integration in all fieldbus systems.

Especificações resumidas

- **Measuring cell** +400 mbar....+400 bar (+6 psi...+6000 psi)

a partir de **R\$ 1.742,46**

Preço a partir de 21.10.2021

Mais informações e preço atual:

www.br.endress.com/PTP31B

Campo de aplicação: The Ceraphant PTP31B is a price-attractive pressure switch with piezoresistive sensor for safe measurement and monitoring of absolute and gauge pressure. The pressure switch with compact design is extremely stable and overload resistant for up to +400 bar. The IO-Link capability allows easy integration and parametrization of the device.

Características e especificações

Pressure

Measuring principle

Pressure switch

Pressure**Characteristic**

Intelligent pressure switch with piezoresistive sensor,
longterm stable and overload resistant

Supply voltage

10...30 VDC

Reference Accuracy

0.5 %,
Platinum: 0.3 %

Long term stability

0.2 % of URL/year

Process temperature

-40 °C...+100 °C
(-40 °F...+212 °F)

Ambient temperature

-20 °C...+70 °C
(-4 °F...+158 °F)

Measuring cell

+400 mbar....+400 bar
(+6 psi...+6000 psi)

Max. overpressure limit

600 bar (9000 psi)

Process connection

Threads:
G1/4, G1/2,
MNPT1/4, MNPT1/2,
DIN13,
JIS R1/2

Pressure

Communication

1x PNP switch
2x PNP switch
1x PNP switch +
4...20mA analogue
AC/DC, DC-PNP
IO-Link

Design approvals

EN 10204-3.1 Final inspection report
Cleaned from oil and grease
Set min alarm

Specialities

Digital display

Mais informações www.br.endress.com/PTP31B