

Suspended solids and color sensor OUSAF12

NIR/VIS absorption sensor for suspended solids and phase detection



Meer informatie en actuele prijzen:

www.be.endress.com/OUSAF12

Voordelen:

- Better product quality monitoring in pharmaceutical and chemical processes
- Cost savings and reduced product loss thanks to fast interphase detection
- Low-maintenance sensor with long service life and stable operation
- Color-independent measurement
- Easy and liquid-free verification
- Suitable for cleaning-in-place (CIP) and sterilization-in-place (SIP)
- Approved for hazardous area use

Overzicht specificaties

- **Measurement range** 0 to 2.5 AU 0 to 50 OD (depending on optical pathlength)
- **Process temperature** 0 to 90 °C (32 to 194 °F) continuous Max. 130 °C (266 °F) for 2 hours
- **Process pressure** Max. 100 bar abs (1450 psi) (depending on flow through assembly)

Toepassingsgebied: OUSAF12 is an optical sensor for the inline detection of suspended solids and product interphases in many industries. It supports you with reliable absorbance measurements to accurately control the quality of products and processes, and to improve production efficiency. OUSAF12 is ready for all kinds of environments, from hazardous areas (ATEX, FM) to hygienic processes (CIP/SIP).

Kenmerken en specificaties

Concentration

MeetprincipeColorimetry

ApplicationColor measurement, measurement of suspended solids, phase separation

Measurement range

0 to 2.5 AU

0 to 50 OD (depending on optical pathlength)

MaterialSensor housing: Stainless Steel 316L

Process temperature

0 to 90 °C (32 to 194 °F) continuous

Max. 130 °C (266 °F) for 2 hours

Process pressure

Max. 100 bar abs (1450 psi)

(depending on flow through assembly)

Ex certification

ATEX II 2G Ex db IIC T5 Gb

FM Cl.1, Div. 1, Group B, C, D

Ingres protectionIP 65 (NEMA 4)

Additional certificationsFDA

Meer informatie www.be.endress.com/OUSAF12