

# Proline Promass H 300 Coriolis flowmeter

Chemically resistant single-tube flowmeter  
with a compact, easily accessible transmitter



Mais informações e preço atual:

[www.br.endress.com/8H3B](http://www.br.endress.com/8H3B)

## Benefícios:

- Maximum safety for chemically aggressive fluids – corrosion-resistant wetted parts
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

## Especificações resumidas

- **Max. measurement error** Mass flow (liquid):  $\pm 0.10\%$  Volume flow (liquid):  $\pm 0.10\%$  Mass flow (gas, Tantalum only):  $\pm 0.50\%$  Density (liquid):  $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 70 000 kg/h (0 to 2570 lb/min)
- **Medium temperature range** Tantalum:  $-50$  to  $+150$  °C ( $-58$  to  $+302$  °F) Zirconium:  $-50$  to  $+205$  °C ( $-58$  to  $+401$  °F)
- **Max. process pressure** PN 40, Class 300, 20K
- **Wetted materials** Measuring tube: Tantalum 2.5W; 702 (UNS R60702) Connection: Tantalum; 702 (UNS R60702)

**Campo de aplicação:** The highly accurate Promass H is destined for applications requiring maximum corrosion resistance and guarantees optimal safety for chemically aggressive fluids. With its compact transmitter Promass H 300 offers high flexibility in terms of operation and system integration: access from one side, remote display and improved connectivity options. Heartbeat Technology ensures process safety at all times.

---

## Características e especificações

---

### Density/Concentration

**Measuring principle**

Coriolis

---

**Product headline**

Chemically resistant single-tube flowmeter with a compact, easily accessible transmitter.

Highly accurate measurement of liquids and gases in applications requiring highest corrosion resistance.

---

**Sensor features**

Maximum safety for chemically aggressive fluids – corrosion - resistant wetted parts. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Measuring tube made of Tantalum, Zirconium. Nominal diameter: DN 8 to 50 ( $\frac{3}{8}$  to 2"). Medium temperature up to +205 °C (+401 °F).

---

**Transmitter features**

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

---

**Nominal diameter range**

DN 8 to 50 ( $\frac{3}{8}$  to 2")

---

**Wetted materials**

Measuring tube: Tantalum 2.5W; 702 (UNS R60702)

Connection: Tantalum; 702 (UNS R60702)

---

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

---

---

## Density/Concentration

**Max. measurement error**Mass flow (liquid):  $\pm 0.10\%$ Volume flow (liquid):  $\pm 0.10\%$ Mass flow (gas, Tantalum only):  $\pm 0.50\%$ Density (liquid):  $\pm 0.0005\text{ g/cm}^3$ 

---

**Measuring range**0 to 70 000 kg/h (0 to 2570 lb/min)

---

**Max. process pressure**PN 40, Class 300, 20K

---

**Medium temperature range**Tantalum:  $-50$  to  $+150\text{ }^\circ\text{C}$  ( $-58$  to  $+302\text{ }^\circ\text{F}$ )Zirconium:  $-50$  to  $+205\text{ }^\circ\text{C}$  ( $-58$  to  $+401\text{ }^\circ\text{F}$ )

---

**Ambient temperature range**Standard:  $-40$  to  $+60\text{ }^\circ\text{C}$  ( $-40$  to  $+140\text{ }^\circ\text{F}$ )Option:  $-50$  to  $+60\text{ }^\circ\text{C}$  ( $-58$  to  $+140\text{ }^\circ\text{F}$ )

---

**Sensor housing material**1.4301 (304), corrosion resistant

---

**Transmitter housing material**AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

---

**Degree of protection**IP66/67, type 4X enclosure

---

**Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

---

**Density/Concentration****Outputs**

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

**Inputs**

Status input

4-20 mA input

**Digital communication**

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

**Power supply**

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

**Hazardous area approvals**

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

**Product safety**

CE, C-tick, EAC marking

**Functional safety**

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Density/Concentration****Pressure approvals and certificates**PED, CRN

---

**Material certificates**3.1 material

---

**Gas****Measuring principle**Coriolis

---

**Product headline**

Chemically resistant single-tube flowmeter with a compact, easily accessible transmitter.

Highly accurate measurement of liquids and gases in applications requiring highest corrosion resistance.

---

**Sensor features**

Maximum safety for chemically aggressive fluids – corrosion - resistant wetted parts. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Measuring tube made of Tantalum, Zirconium. Nominal diameter: DN 8 to 50 ( $\frac{3}{8}$  to 2"). Medium temperature up to +205 °C (+401 °F).

---

**Transmitter features**

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

---

**Nominal diameter range**DN 8 to 50 ( $\frac{3}{8}$  to 2")

---

**Wetted materials**

Measuring tube: Tantalum 2.5W; 702 (UNS R60702)

Connection: Tantalum; 702 (UNS R60702)

---

## Gas

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

**Max. measurement error**

Mass flow (liquid):  $\pm 0.10$  %

Volume flow (liquid):  $\pm 0.10$  %

Mass flow (gas, Tantalum only):  $\pm 0.50$  %

Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

**Measuring range**

0 to 70 000 kg/h (0 to 2570 lb/min)

**Max. process pressure**

PN 40, Class 300, 20K

**Medium temperature range**

Tantalum:  $-50$  to  $+150$  °C ( $-58$  to  $+302$  °F)

Zirconium:  $-50$  to  $+205$  °C ( $-58$  to  $+401$  °F)

**Ambient temperature range**

Standard:  $-40$  to  $+60$  °C ( $-40$  to  $+140$  °F)

Option:  $-50$  to  $+60$  °C ( $-58$  to  $+140$  °F)

**Sensor housing material**

1.4301 (304), corrosion resistant

**Transmitter housing material**

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

**Degree of protection**

IP66/67, type 4X enclosure

**Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

**Gas****Outputs**

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

**Inputs**

Status input

4-20 mA input

**Digital communication**

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

**Power supply**

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

**Hazardous area approvals**

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

**Product safety**

CE, C-tick, EAC marking

**Functional safety**

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Gas****Pressure approvals and certificates**

PED, CRN

---

**Material certificates**

3.1 material

---

**Density****Measuring principle**

Coriolis

---

**Product Headline**

Chemically resistant single-tube flowmeter with a compact, easily accessible transmitter.

Highly accurate measurement of liquids and gases in applications requiring highest corrosion resistance.

---

**Sensor features**

Maximum safety for chemically aggressive fluids – corrosion - resistant wetted parts. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Measuring tube made of Tantalum, Zirconium. Nominal diameter: DN 8 to 50 ( $\frac{3}{8}$  to 2"). Medium temperature up to +205 °C (+401 °F).

---

**Transmitter features**

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

---

**Liquids****Measuring principle**

Coriolis



## Liquids

### Product headline

Chemically resistant single-tube flowmeter with a compact, easily accessible transmitter.

Highly accurate measurement of liquids and gases in applications requiring highest corrosion resistance.

### Sensor features

Maximum safety for chemically aggressive fluids – corrosion - resistant wetted parts. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Measuring tube made of Tantalum, Zirconium. Nominal diameter: DN 8 to 50 ( $\frac{3}{8}$  to 2"). Medium temperature up to +205 °C (+401 °F).

### Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

### Nominal diameter range

DN 8 to 50 ( $\frac{3}{8}$  to 2")

### Wetted materials

Measuring tube: Tantalum 2.5W; 702 (UNS R60702)

Connection: Tantalum; 702 (UNS R60702)

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

### Max. measurement error

Mass flow (liquid):  $\pm 0.10$  %

Volume flow (liquid):  $\pm 0.10$  %

Mass flow (gas, Tantalum only):  $\pm 0.50$  %

Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

## Liquids

**Measuring range**

0 to 70 000 kg/h (0 to 2570 lb/min)

---

**Max. process pressure**

PN 40, Class 300, 20K

---

**Medium temperature range**

Tantalum: -50 to +150 °C (-58 to +302 °F)

Zirconium: -50 to +205 °C (-58 to +401 °F)

---

**Ambient temperature range**

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

---

**Sensor housing material**

1.4301 (304), corrosion resistant

---

**Transmitter housing material**

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

---

**Degree of protection**

IP66/67, type 4X enclosure

---

**Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

---

**Outputs**

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

---

## Liquids

### Inputs

Status input

4-20 mA input

### Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

### Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

### Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

### Product safety

CE, C-tick, EAC marking

### Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

### Pressure approvals and certificates

PED, CRN

### Material certificates

3.1 material

Mais informações [www.br.endress.com/8H3B](http://www.br.endress.com/8H3B)