

Proline Prowirl F 200

Vortex-flowmeter

Veelzijdige flowmeter met detectie van natte stoom en hoogste nauwkeurigheid



Meer informatie en actuele prijzen:

www.be.endress.com/7F2C

Voordelen:

- Eenvoudig energiemanagement – geïntegreerde temperatuur- en drukmeting voor stoom en gas
- Ruimtebesparend ontwerp – inlaatlengtecompensatie
- Gelijke nauwkeurigheid tot Re 10 000 – uiterst lineair Vortex-meterlichaam
- Langdurige stabiliteit – robuuste capacitieve sensor zonder afwijking
- Handige instrumentbedrading – gescheiden aansluitcompartiment
- Veilige bediening – geen noodzaak om het instrument te openen dankzij display met aanraakbediening en achtergrondverlichting
- Geïntegreerde verificatie – Heartbeat Technology

Overzicht specificaties

- **Max. meetfout** Volume flow (liquid): $\pm 0.75\%$ Volume flow (optional): $\pm 0.65\%$ Volume flow (optional): $\pm 0.65\%$ Volume flow (steam, gas): $\pm 1.00\%$ Mass flow (saturated steam): $\pm 1.7\%$ (temperature compensated); $\pm 1.5\%$ (temperature/pressure compensated) Mass flow (superheated steam, gas): ± 1.5 (temperature/pressure compensated); $\pm 1.7\%$ (temperature compensated + external pressure compensation) Mass flow (liquid): $\pm 0.85\%$
- **Measuring range** Liquid: 0.076 to 2100 m³/h (0.045 to 1300 ft³/min) depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F) Steam, gas: 0.39 to 28000 m³/h (0.23 to 17000 ft³/min) depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a); air with 25 °C, 4.4 bar a (77 °F, 63.8 psi a)

Medium temperature range Standard: -40 to +260 °C (-40 to +500 °F) High/low temperature (option): -200 to +400 °C (-328 to +752 °F)

- **Max. process pressure** PN 100, Class 600, 20K
- **Wetted materials** Measuring tube: 1.4408 (C3FM); CX2MW similar to Alloy C22, 2.4602 DSC sensor: 1.4404 (316/316L); UNS N06022 similar to Alloy C22, 2.4602 Process connection: 1.4404/F316/F316L); 2.4602

Toepassingsgebied: Prowirl F is de multivariabele flowmeter met inline natte-stoommeting. De kalibratie-optie PremiumCal garandeert een uitstekende meetnauwkeurigheid en optimale beschikbaarheid van de installatie bij lage flows van gas, stoom en vloeistoffen. Dankzij de echte lusgevoede technologie zorgt de Prowirl F 200 voor een kosteneffectieve en naadloze integratie in bestaande infrastructuren. Deze biedt maximale operationele veiligheid in gevaarlijke omgevingen. Heartbeat Technology waarborgt te allen tijde de procesveiligheid.

Kenmerken en specificaties

Steam

Meetprincipe

Vortex

Product headline

Versatile flowmeter with detection of wet steam conditions and best-in-class accuracy.

Easy energy management – integrated temperature and pressure measurement for steam and gases.

Suitable for a wide range of applications; optimized for steam applications.

Sensor features

Space-saving engineering – inlet run compensation. Same accuracy down to Re 10 000 – most linear Vortex meter body. Long-term stability – robust drift-free capacitive sensor.

Wet steam capabilities for DN 25 to 300 (1 to 12"). Flexible positioning of pressure cell. Industrial siphon design for pressure measurement.

Steam

Transmitter features

Convenient device wiring – separate connection compartment. Safe operation – no need to open the device due to display with touch control, background lighting. Integrated verification – Heartbeat Technology. Display module with data transfer function. Robust dual-compartment housing. Plant safety: worldwide approvals (SIL, Haz. area).

Nominal diameter range

DN 15 to 300 (½ to 12")

Wetted materials

Measuring tube: 1.4408 (C3FM); CX2MW similar to Alloy C22, 2.4602
DSC sensor: 1.4404 (316/316L); UNS N06022 similar to Alloy C22, 2.4602

Process connection: 1.4404/F316/F316L); 2.4602

Measured variables

Volume flow, mass flow, corrected volume flow, energy flow, heat flow difference, temperature

Max. meetfout

Volume flow (liquid): $\pm 0.75\%$

Volume flow (optional): $\pm 0.65\%$

Volume flow (optional): $\pm 0.65\%$

Volume flow (steam, gas): $\pm 1.00\%$

Mass flow (saturated steam): $\pm 1.7\%$ (temperature compensated); $\pm 1.5\%$ (temperature/pressure compensated)

Mass flow (superheated steam, gas): ± 1.5 (temperature/pressure compensated); $\pm 1.7\%$ (temperature compensated + external pressure compensation)

Mass flow (liquid): $\pm 0.85\%$

Measuring range

Liquid: 0.076 to 2100 m³/h (0.045 to 1300 ft³/min)

depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F)

Steam, gas: 0.39 to 28000 m³/h (0.23 to 17000 ft³/min)

depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a);

air with 25 °C, 4.4 bar a (77 °F, 63.8 psi a)

Steam

Max. process pressure

PN 100, Class 600, 20K

Medium temperature range

Standard: -40 to +260 °C (-40 to +500 °F)

High/low temperature (option): -200 to +400 °C (-328 to +752 °F)

Ambient temperature range

Compact version (standard): -40 to +80 °C (-40 to +176 °F)

Compact version (option): -50 to +80 °C (-58 to +176 °F)

Remote version (standard): -40 to +85 °C (-40 to +185 °F)

Remote version (option): -50 to +85 °C (-58 to +185 °F)

Sensor housing material

Sensor connection housing: AlSi10Mg, coated; 1.4408 (CF3M)

Transmitter housing material

AlSi10Mg, coated; 1.4404 (316L)

Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version: IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

4 - 20 mA HART (passive)

4 - 20 mA (passive)

Pulse/frequency/switch output (passive)

Inputs

Current Input 4 - 20 mA (passive)

Steam**Digital communication**

HART, PROFIBUS PA, FOUNDATION Fieldbus

Power supply

DC 12 to 35 V (4 - 20 mA HART with/without pulse/frequency/switch output)

DC 12 to 30 V (4 - 20 mA HART, 4 - 20 mA)

DC 12 to 35 V (4 - 20 mA HART, pulse/frequency/switch output, 4 - 20 mA input)

DC 9 to 32 V (PROFIBUS PA, pulse/frequency/switch output)

Hazardous area approvals

ATEX, IECEx, cCSAus, JPN, EAC, UK Ex

Product safety

CE, C-TICK, EAC

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS, LR, BV, DNV GL

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI (on request); welding test acc. to ISO 15614 - 1, similar to ASME IX (on request)

Liquids

Meetprincipe

Vortex

Product headline

Versatile flowmeter with detection of wet steam conditions and best-in-class accuracy.

Easy energy management – integrated temperature and pressure measurement for steam and gases.

Suitable for a wide range of applications; optimized for steam applications.

Sensor features

Space-saving engineering – inlet run compensation. Same accuracy down to Re 10 000 – most linear Vortex meter body. Long-term stability – robust drift-free capacitive sensor.

Wet steam capabilities for DN 25 to 300 (1 to 12"). Flexible positioning of pressure cell. Industrial siphon design for pressure measurement.

Sensor features

Space-saving engineering – inlet run compensation. Same accuracy down to Re 10 000 – most linear Vortex meter body. Long-term stability – robust drift-free capacitive sensor.

Wet steam capabilities for DN 25 to 300 (1 to 12"). Flexible positioning of pressure cell. Industrial siphon design for pressure measurement.

Transmitter features

Convenient device wiring – separate connection compartment. Safe operation – no need to open the device due to display with touch control, background lighting. Integrated verification – Heartbeat Technology. Display module with data transfer function. Robust dual-compartment housing. Plant safety: worldwide approvals (SIL, Haz. area).

Transmitter features

Convenient device wiring – separate connection compartment. Safe operation – no need to open the device due to display with touch control, background lighting. Integrated verification – Heartbeat Technology. Display module with data transfer function. Robust dual-compartment housing. Plant safety: worldwide approvals (SIL, Haz. area).

Liquids

Nominal diameter range

DN 15 to 300 (½ to 12")

Wetted materials

Measuring tube: 1.4408 (C3FM); CX2MW similar to Alloy C22, 2.4602
DSC sensor: 1.4404 (316/316L); UNS N06022 similar to Alloy C22,
2.4602

Process connection: 1.4404/F316/F316L); 2.4602

Measured variables

Volume flow, mass flow, corrected volume flow, energy flow, heat flow
difference, temperature

Max. meetfout

Volume flow (liquid): ± 0.75 %

Volume flow (optional): ± 0.65 %

Volume flow (steam, gas): ± 1.00 %

Mass flow (saturated steam): ± 1.7 % (temperature compensated); ± 1.5 %
(temperature/pressure compensated)

Mass flow (superheated steam, gas): ± 1.5 (temperature/pressure
compensated); ± 1.7 % (temperature compensated + external pressure
compensation)

Mass flow (liquid): ± 0.85 %

Measuring range

Liquid: 0.076 to 2100 m³/h (0.045 to 1300 ft³/min)

depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F)

Steam, gas: 0.39 to 28000 m³/h (0.23 to 17000 ft³/min)

depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a);
air with 25 °C, 4.4 bar a (77 °F, 63.8 psi a)

Max. process pressure

PN 100, Class 600, 20K

Medium temperature range

Standard: -40 to +260 °C (-40 to +500 °F)

High/low temperature (option): -200 to +400 °C (-328 to +752 °F)

Liquids

Ambient temperature range

Compact version (standard): -40 to +80 °C (-40 to +176 °F)

Compact version (option): -50 to +80 °C (-58 to +176 °F)

Remote version (standard): -40 to +85 °C (-40 to +185 °F)

Remote version (option): -50 to +85 °C (-58 to +185 °F)

Sensor housing material

Sensor connection housing: AlSi10Mg, coated; 1.4408 (CF3M)

Transmitter housing material

AlSi10Mg, coated; 1.4404 (316L)

Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version: IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

4 - 20 mA HART (passive)

4 - 20 mA (passive)

Pulse/frequency/switch output (passive)

Inputs

Current Input 4 - 20 mA (passive)

Digital communication

HART, PROFIBUS PA, FOUNDATION Fieldbus

Liquids

Power supply

DC 12 to 35 V (4 - 20 mA HART with/without pulse/frequency/switch output)

DC 12 to 30 V (4 - 20 mA HART, 4 - 20 mA)

DC 12 to 35 V (4 - 20 mA HART, pulse/frequency/switch output, 4 - 20 mA input)

DC 9 to 32 V (PROFIBUS PA, pulse/frequency/switch output)

Hazardous area approvals

ATEX, IECEx, cCSAus, JPN, EAC

Product safety

CE, C-TICK, EAC, UK Ex

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS, LR, BV, DNV GL

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI (on request); welding test acc. to ISO 15614 - 1, similar to ASME IX (on request)

Gas

Meetprincipe

Vortex

Product headline

Versatile flowmeter with detection of wet steam conditions and best-in-class accuracy.

Easy energy management – integrated temperature and pressure measurement for steam and gases.

Suitable for a wide range of applications; optimized for steam applications.

Sensor features

Space-saving engineering – inlet run compensation. Same accuracy down to Re 10 000 – most linear Vortex meter body. Long-term stability – robust drift-free capacitive sensor.

Wet steam capabilities for DN 25 to 300 (1 to 12"). Flexible positioning of pressure cell. Industrial siphon design for pressure measurement.

Transmitter features

Convenient device wiring – separate connection compartment. Safe operation – no need to open the device due to display with touch control, background lighting. Integrated verification – Heartbeat Technology. Display module with data transfer function. Robust dual-compartment housing. Plant safety: worldwide approvals (SIL, Haz. area).

Nominal diameter range

DN 15 to 300 (½ to 12")

Wetted materials

Measuring tube: 1.4408 (C3FM); CX2MW similar to Alloy C22, 2.4602

Measured variables

Volume flow, mass flow, corrected volume flow, energy flow, heat flow difference, temperature

Gas

Max. meetfoutVolume flow (liquid): $\pm 0.75\%$ Volume flow (optional): $\pm 0.65\%$ Volume flow (steam, gas): $\pm 1.00\%$ Mass flow (saturated steam): $\pm 1.7\%$ (temperature compensated); $\pm 1.5\%$ (temperature/pressure compensated)Mass flow (superheated steam, gas): ± 1.5 (temperature/pressure compensated); $\pm 1.7\%$ (temperature compensated + external pressure compensation)Mass flow (liquid): $\pm 0.85\%$ **Measuring range**Liquid: 0.076 to 2100 m³/h (0.045 to 1300 ft³/min)

depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F)

Steam, gas: 0.39 to 28000 m³/h (0.23 to 17000 ft³/min)depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a);
air with 25 °C, 4.4 bar a (77 °F, 63.8 psi a)**Max. process pressure**

PN 100, Class 600, 20K

Medium temperature range

Standard: -40 to +260 °C (-40 to +500 °F)

High/low temperature (option): -200 to +400 °C (-328 to +752 °F)

Ambient temperature range

Compact version (standard): -40 to +80 °C (-40 to +176 °F)

Compact version (option): -50 to +80 °C (-58 to +176 °F)

Remote version (standard): -40 to +85 °C (-40 to +185 °F)

Remote version (option): -50 to +85 °C (-58 to +185 °F)

Sensor housing material

Sensor connection housing: AlSi10Mg, coated; 1.4408 (CF3M)

Transmitter housing material

AlSi10Mg, coated; 1.4404 (316L)

Gas

Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version: IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

4 - 20 mA HART (passive)

4 - 20 mA (passive)

Pulse/frequency/switch output (passive)

Inputs

Current Input 4 - 20 mA (passive)

Digital communication

HART, PROFIBUS PA, FOUNDATION Fieldbus

Power supply

DC 12 to 35 V (4 - 20 mA HART with/without pulse/frequency/switch output)

DC 12 to 30 V (4 - 20 mA HART, 4 - 20 mA)

DC 12 to 35 V (4 - 20 mA HART, pulse/frequency/switch output, 4 - 20 mA input)

DC 9 to 32 V (PROFIBUS PA, pulse/frequency/switch output)

Hazardous area approvals

ATEX, IECEx, cCSAus, JPN, EAC, UK Ex

Product safety

CE, C-TICK, EAC

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Gas

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS, LR, BV, DNV GL

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI (on request); welding test acc. to ISO 15614 - 1, similar to ASME IX (on request)

Meer informatie www.be.endress.com/7F2C