

# TST41N

## Modular RTD thermometer

Comprehensive and common temperature measurement technology for almost all branches of industry



Mais informações e preço atual:

[www.br.endress.com/TST41N](http://www.br.endress.com/TST41N)

### Benefícios:

- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- High degree of insert compatibility and design as per DIN 43772
- Fast response time with reduced/tapered tip form
- Head transmitter with easy selection: Analog output 4 to 20 mA, HART®, PROFIBUS® PA or FOUNDATION Fieldbus™

### Especificações resumidas

- **Accuracy** class A acc. to IEC 60751 class AA acc. to IEC 60751
- **Response time** depending on configuration  $t_{50} = 3$  s  $t_{90} = 6$  s
- **Max. process pressure (static)** at 20 °C: 20 bar (290 psi)
- **Operating temperature range** PT 100: -50 °C ... 600 °C (-58 °F ... 1.112 °F)
- **Max. immersion length on request** up to 10.000,00 mm (393,70")

**Campo de aplicação:** The thermometer is mainly used in the chemical industry but also finds its use in other branches. The device with head transmitter is a complete unit ready for use with enhanced measurement accuracy and reliability compared to directly wired sensors. A variety of process connections, dimensions and materials offer flexible application possibilities.

### Características e especificações

---

**Thermometer****Measuring principle**Resistance Temperature Detector

---

**Characteristic / Application**

metric style  
modular temperature assembly  
fast response time (reduced/tapered tip)  
threaded process connection  
without neck

---

**Thermowell / protection tube**without (not intended to use with thermowell)

---

**Insert / probe**mineral insulated (MI), flexible

---

**Outer diameter protection tube / Insert**

6,0 mm (0,24")  
9,0 mm (0,35")

---

**Max. immersion length on request**up to 10.000,00 mm (393,70")

---

**Material protection tube/ thermowell**1.4404 (316L)

---

**Process connection**

male thread:

G1/2"

G3/4"

G1"

NPT1/2"

NPT3/4"

NPT1"

M20x1.5

---

**Tip shape**reduced

---

## Thermometer

**Surface roughness Ra**

0,8 µm (31,5 µin.)

**Operating temperature range**

PT 100:

-50 °C ... 600 °C

(-58 °F ... 1.112 °F)

**Max. process pressure (static)**

at 20 °C: 20 bar (290 psi)

**Accuracy**

class A acc. to IEC 60751

class AA acc. to IEC 60751

**Response time**

depending on configuration

t50 = 3 s

t90 = 6 s

**Integration head transmitter**yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)Mais informações [www.br.endress.com/TST41N](http://www.br.endress.com/TST41N)