

## Radiometric level and density measurement Gamma Source FSG60

Gamma radiation source ( $^{137}\text{Cs}$ ) for radiometric level, point level, density and interface measurement



### Benefícios:

- Specially constructed source capsule conforms to strictest safety requirements:  
Typically class C66646 to ISO 2919
- Point source in special source container ensures simple handling and easy installation
- Choice of activity ensures optimized dosage for your application
- High cost-effectiveness due to long half-life time

### Especificações resumidas

- **Process pressure absolute / max. overpressure limit** Any

Mais informações e preço atual:

[www.br.endress.com/FSG60](http://www.br.endress.com/FSG60)

**Campo de aplicação:** The Gamma Source FSG60 has a very long lifetime thanks to its long half-life time. Common used standard isotope in the industrial process measurement.

## Características e especificações

Continuous / Solids

### Measuring principle

Radiometric

### Characteristic / Application

Source

Isotope: Caesium 137

Half-life: 30 years

---

**Continuous / Solids****Specialities**

Double seal  
Steel: 1.4541 (321 S 18)  
Classification C66646 ISO 2919  
Activity calculation with  
Applicator

---

**Ambient temperature**

-20°C ... +250 °C  
(-4°F ... 482 °F)

---

**Process pressure absolute / max. overpressure  
limit**

Any

---

**Components**

Installed in source container

---

**Density****Measuring principle**

Radiometric Density

---

**Characteristic / Application**

Source  
Isotope: Caesium 137  
Half-life: 30 years

---

**Ambient temperature**

-20 °C ... +250 °C

---

**Specialities**

Double seal  
Steel: 1.4541 (321 S 18)  
Classification: C66646 ISO  
2919  
Activity calculation with  
Applicator

---

---

**Density****Components**Installed in source container

---

**Point Level / Solids****Measuring principle**Radiometric Limit

---

**Characteristic / Application**

Source

Isotope: Caesium 137

Half-life: 30 years

---

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification C66646 ISO 2919

Activity calculation with

Applicator

---

**Ambient temperature**

-20°C ... +250 °C

(-4°F ... 482 °F)

---

**Process pressure absolute / max. overpressure  
limit**Any

---

**Components**Installed in source container

---

**Point Level / Liquids****Measuring principle**Radiometric Limit

---

---

**Point Level / Liquids****Characteristic / Application**

Source  
Isotope: Caesium 137  
Half-life: 30 years

---

**Specialities**

Double seal  
Steel: 1.4541 (321 S 18)  
Classification C66646 ISO 2919  
Activity calculation with  
Applicator

---

**Ambient temperature**

-20°C ... +250 °C  
(-4°F ... 482 °F)

---

**Process pressure absolute / max. overpressure  
limit**

Any

---

**Components**

Installed in source container

---

**Continuous / Liquids****Measuring principle**

Radiometric

---

**Characteristic / Application**

Source  
Isotope: Caesium 137  
Half-life: 30 years

---

**Specialities**

Double seal  
Steel: 1.4541 (321 S 18)  
Classification C66646 ISO 2919

---

## Continuous / Liquids

### Ambient temperature

-20°C ... +250 °C

(-4°F ... 482 °F)

---

### Process pressure absolute / max. overpressure

limit

Any

---

### Pressure measuring range

Any

---

### Components

Installed in source container

---

Mais informações [www.br.endress.com/FSG60](http://www.br.endress.com/FSG60)