

# Electromechanical Level measurement Silopilot FMM20

Basic model for continuous level measurement  
in light bulk solids



Mais informações e preço atual:

[www.br.endress.com/FMM20](http://www.br.endress.com/FMM20)

## Benefícios:

- Tried and tested, reliable measurement of light bulk solids, e.g. cereals, plastic granulate, powder
- Safe measurements in extremely dusty environments
- Fully electronic digital minimum fail-safe control, therefore no running down of the sensor weight into the silo outlet and no risk to the conveying systems
- Quick menu-guided local operation using a 4-line text display
- Supply voltage 90 to 253VAC (wide-range voltage power unit) as well as 24VDC, depending on version selected

## Especificações resumidas

- **Accuracy** +/- 2.5 cm (0.98")
- **Process temperature** -20°C ... +150°C (-4°F...302°F)
- **Process pressure absolute / max. overpressure limit** 0.8 ... 1.1 bar (11.6psi...15.95psi)
- **Max. measurement distance** 32m (105ft)
- **Main wetted parts** Aluminium, Steel, Stainless steel

**Campo de aplicação:** Silopilot FMM20 is a low cost device for electromechanical level measurement in bins or silos with dusty, fine-grained or coarse grained bulk solids or in tanks with liquids.

## Características e especificações

## Continuous / Solids

**Measuring principle**

Electromechanical

**Characteristic / Application**

Not affected by characteristics of solid medium

Measuring range: 32m

**Specialities**

Switch to indicate need of maintenance (predictive maintenance)

**Supply / Communication**

90... 253V, 50/60Hz

20 - 28 VDC

**Accuracy**

+/- 2.5 cm (0.98")

**Ambient temperature**

-40°C ... +60°C

(-40°F...140°F)

**Process temperature**

-20°C ... +150°C

(-4°F...302°F)

**Process pressure absolute / max. overpressure limit**

0.8 ... 1.1 bar

(11.6psi...15.95psi)

**Main wetted parts**

Aluminium, Steel, Stainless steel

**Process connection**

Flange DN100 PN16 / 4"

**Blocking distance**

Top: 500mm (20")

Continuous / Solids

**Max. measurement distance**

32m (105ft)

---

**Communication**

0/4...20 mA

---

**Certificates / Approvals**

ATEX

---

Mais informações [www.br.endress.com/FMM20](http://www.br.endress.com/FMM20)