

Guided radar measurement Time-of-Flight Levelflex FMP56

Economically efficient basis model for all level applications in bulk solids



Benefícios:

- Reliable measurement even for changing product and process conditions
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Highest reliability due to new Multi-Echo Tracking evaluation
- Hardware and software developed according to IEC 61508 up to SIL3
- Heartbeat Technology for a cost-effective and safe plant operation during the entire life cycle
- Seamless integration into control or asset management systems and intuitive, menu-guided operation concept (on-site or via the control system)
- World's easiest proof test for SIL and WHG saves time and costs

Mais informações e preço atual:

www.br.endress.com/FMP56

Especificações resumidas

- **Accuracy** Rope probe: +/- 2 mm (0.08 in)
- **Process temperature** -40...+120 °C (-40...+248 °F)
- **Process pressure absolute / max. overpressure limit**
Vacuum...16 bar (Vacuum...232 psi)
- **Max. measurement distance** Rope: 12 m (40 ft) Min DK>1.4
- **Main wetted parts** Rope probe: 304, 316, 316Ti, 316L, PEEK, PPS, PA

Campo de aplicação: Levelflex FMP56 is particularly designed for light-duty process conditions as they occur in silos and storage tanks for solids. FMP56 guided radar offers maximum reliability even in case of dusty atmosphere in narrow silos or in vessels with obstacles. Levelflex FMP56 is used for continuous level measurement in powdery to granular bulk

solids. Dust, filling noises, temperature layers and gas layers do not affect the measurement.

Características e especificações

Continuous / Solids

Measuring principle

Guided radar

Characteristic / Application

Basic device for pulling forces up to 12kN

Rope probe

Integrated data memory, Factory precalibrated, Reliable measuring: in dusty atmosphere, in high + narrow silos, in vessels + obstacles.

Specialities

Heartbeat Technology,

Bluetooth® commissioning,

Operation and maintenance SmartBlue App,

HistoROM,

RFID TAG for easy identification

Supply / Communication

2-wire (HART / PROFIBUS PA/ FOUNDATION Fieldbus),

4-wire (HART),

Bluetooth® wireless technology and App (optional)

Accuracy

Rope probe: +/- 2 mm (0.08 in)

Continuous / Solids

Ambient temperature

-40...+80 °C

(-40...+176 °F)

Process temperature

-40...+120 °C

(-40...+248 °F)

Process pressure absolute / max. overpressure limit

Vacuum...16 bar

(Vacuum...232 psi)

Main wetted parts

Rope probe:

304, 316, 316Ti, 316L, PEEK, PPS, PA

Process connection

Thread:

G 3/4, MNPT 3/4

Sensor length

Rope probe: 12 m (40 ft)

Max. measurement distance

Rope: 12 m (40 ft) Min DK>1.4

Continuous / Solids

Communication

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Bluetooth® wireless technology

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, KC, EAC

Safety approvals

SIL

Options

Sensor remote with 3 m/ 9 ft cable,

Remote operation via SmartBlue App using Bluetooth®

Mais informações www.br.endress.com/FMP56