

TAF12D

High temperature TC thermometer

Applicable for ceramic baking ovens, brickworks, porcelain production and glass industries



Mais informações e preço atual:

www.br.endress.com/TAF12D

Benefícios:

- Long lifetime by usage of innovative thermowell materials with increased wear and chemical resistance
- Long term stable measurement due to sensor protection with non-porous materials
- Flexible product selection by modular design
- Optimized life cycle costs by means of replaceable spare parts

Especificações resumidas

- **Accuracy** class 2 acc. to IEC 60584
- **Max. process pressure (static)** at 20 °C: 1 bar (15 psi)
- **Operating temperature range** Type S: 0 C ...1.600 C (32 F ...2.912 F) Type R: 0 C ...1.600 C (32 F ...2.912 F) Type B: 600 C ...1.700 C (1.112 F ...3.092 F)
- **Max. immersion length on request** up to 3.500,00 mm (137,80")

Campo de aplicação: Measuring points with extremely high process temperatures require these special thermometers with ceramic thermowells and thermocouples made from special metals, such as platinum and rhodium. The thermowell and the internal sheath made from ceramic materials protects from mechanical and chemical damages in the process and increases the life span of the sensors. This leads to: Cost savings for maintenance of the measuring point, quality improvements of the products and increased plant safety.

Características e especificações

Thermometer**Measuring principle**Thermocouple

Characteristic / Application

metric style

modular temperature assembly

high temperature probe (furnace)

incl. double ceramic thermowell

Thermowell / protection tubeceramic protection tube and inner tube

Insert / probeceramic capillary, rigid

Outer diameter protection tube / Insert

14,0 mm (0,55")

15,0 mm (0,59")

Max. immersion length on requestup to 3.500,00 mm (137,80")

Material protection tube/ thermowellCeramic (C610/C799)

Thermometer

Process connection

compression fitting:

G3/4"

G1"

G1 1/2"

adjustable Flange

Tip shape

straight

Operating temperature range

Type S:

0 C ...1.600 C

(32 F ...2.912 F)

Type R:

0 C ...1.600 C

(32 F ...2.912 F)

Type B:

600 C ...1.700 C

(1.112 F ...3.092 F)

Max. process pressure (static)

at 20 °C: 1 bar (15 psi)

Accuracy

class 2 acc. to IEC 60584

Thermometer

Integration head transmitter

yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Certification

SIL (transmitter only)

Mais informações www.br.endress.com/TAF12D