

# TU51 Weld-in barstock thermowell, US style

## Thermowell with weld-in process connections and round extension



Mais informações e preço atual:

[www.br.endress.com/TU51](http://www.br.endress.com/TU51)

### Benefícios:

- Extension, immersion length and total length can be chosen according to process requirements
- Modular configuration enable a use in all industrial processes with severe thermal and mechanical stresses
- Fast response time with conical tip form

### Especificações resumidas

- **Max. process pressure (static)** 500 bar (7252 psi)
- **Maximum standard immersion length** 24"

**Campo de aplicação:** The robust thermowell is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas and Energy industry. Harsh environments, corrosive substances and highest pressures can be handled by the use of robust protection tubes and special materials.

## Características e especificações

### Thermowell

#### Measuring principle

Bar stock Thermowell

#### Characteristic / Application

US-style

weld-in process connections

## Thermowell

**Head connection**

internal thread:

1/2" NPT

**Maximum standard immersion length**

24"

**Process connection**

weld-in

**Thermowell root diameter**

1.050"

1.315"

**Medium contact material**

316/ 316L

others on request

**Wetted part finishing (Ra)**

32 µin (0.80 µin)

**Tip shape**

tapered

**Temperature range**

-200...700 °C (-328...1.292 °F)

**Max. process pressure (static)**

500 bar (7252 psi)

**Max. process pressure at 400 °C**

depends on configuration

Mais informações [www.br.endress.com/TU51](http://www.br.endress.com/TU51)