

# CNGmass D8CB Coriolis flowmeter

## Refueling application flowmeter with easy system integration



Mais informações e preço atual:

[www.br.endress.com/D8CB](http://www.br.endress.com/D8CB)

### Benefícios:

- Excellent operational safety – reliable under extreme process conditions
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Space-saving transmitter – full functionality on the smallest footprint
- Fast commissioning – pre-configured devices
- Automatic recovery of data for servicing

### Especificações resumidas

- **Max. measurement error** Mass flow:  $\pm 0.5$  % of batch
- **Measuring range** 0 to 150 kg/min (0 to 330 lb/min)
- **Medium temperature range**  $-50$  to  $+125$  °C ( $-58$  to  $+257$  °F)
- **Max. process pressure** 350 bar (5080 psi)
- **Wetted materials** Measuring tube: 1.4435 (316L) Connection: 1.4404 (316/316L)

**Campo de aplicação:** The market for natural gas is still growing! Compressed natural gas has long been established as an alternative fuel for vehicles. Compressed natural gas is also considered the cleanest fuel for combustion engines. The new CNGmass is specially designed for dispensers. With this Coriolis flowmeter the mass flow can be measured with highest accuracy – independent of pressure and temperature.

### Características e especificações

## Liquids

### Measuring principle

Coriolis

---

### Product headline

The refueling application flowmeter with seamless system integration. Accurate measurement of compressed natural gas (CNG) in high pressure refueling applications.

---

### Sensor features

Excellent operational safety – reliable under extreme process conditions. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in/outlet run needs. Flow rates up to 150 kg/min (330 lb/min). Process pressure up to 350 bar (5080 psi).

---

### Transmitter features

Space - saving transmitter – full functionality on the smallest footprint. Fast commissioning – pre - configured devices. Automatic recovery of data for servicing. Robust, compact transmitter housing. Modbus RS485.

---

### Nominal diameter range

DN 8 to 25 ( $\frac{3}{8}$  to 1")

---

### Wetted materials

Mesuring tube: 1.4435 (316L)

Connection: 1.4404 (316/316L)

---

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

---

### Max. measurement error

Mass flow:  $\pm 0.5$  % of batch

---

### Measuring range

0 to 150 kg/min (0 to 330 lb/min)

---

### Max. process pressure

350 bar (5080 psi)

---

Liquids

**Medium temperature range**  
-50 to +125 °C (-58 to +257 °F)

**Ambient temperature range**  
-40 to +60 °C (-40 to +140 °F)

**Sensor housing material**  
1.4301 (304), corrosion resistant

**Transmitter housing material**  
AlSi10Mg, coated

**Degree of protection**  
IP66/67, type 4X enclosure

**Display/Operation**  
No local operation  
Configuration via operating tools possible

**Outputs**  
None

**Inputs**  
None

**Digital communication**  
Modbus RS485

**Power supply**  
DC 20 to 30 V

**Hazardous area approvals**  
ATEX, IECEx, cCSAus, NEPSI, INMETRO

**Metrological approvals and certificates**  
Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

---

**Liquids****Pressure approvals and certificates**CRN

---

**Material certificates**3.1 material

---

**Gas****Measuring principle**Coriolis

---

**Product headline**

The refueling application flowmeter with seamless system integration. Accurate measurement of compressed natural gas (CNG) in high pressure refueling applications.

---

**Sensor features**

Excellent operational safety – reliable under extreme process conditions. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in/outlet run needs. Flow rates up to 150 kg/min (330 lb/min). Process pressure up to 350 bar (5080 psi).

---

**Transmitter features**

Space - saving transmitter – full functionality on the smallest footprint. Fast commissioning – pre - configured devices. Automatic recovery of data for servicing. Robust, compact transmitter housing. Modbus RS485.

---

**Nominal diameter range**DN 8 to 25 ( $\frac{3}{8}$  to 1")

---

**Wetted materials**

Measuring tube: 1.4435 (316L)

Connection: 1.4404 (316/316L)

---

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

---

## Gas

**Max. measurement error**

Mass flow:  $\pm 0.5$  % of batch

---

**Measuring range**

0 to 150 kg/min (0 to 330 lb/min)

---

**Max. process pressure**

350 bar (5080 psi)

---

**Medium temperature range**

-50 to +125 °C (-58 to +257 °F)

---

**Ambient temperature range**

-40 to +60 °C (-40 to +140 °F)

---

**Sensor housing material**

1.4301 (304), corrosion resistant

---

**Transmitter housing material**

AlSi10Mg, coated

---

**Degree of protection**

IP66/67, type 4X enclosure

---

**Display/Operation**

No local operation

Configuration via operating tools possible

---

**Outputs**

None

---

**Inputs**

None

---

**Digital communication**

Modbus RS485

---

**Power supply**

DC 20 to 30 V

---

## Gas

### **Hazardous area approvals**

ATEX, IECEx, cCSAus, NEPSI, INMETRO

---

### **Other approvals and certificates**

3.1 material, calibration performed on accredited calibration facilities  
(acc. to ISO/IEC 17025)

CRN

---

Mais informações [www.br.endress.com/D8CB](http://www.br.endress.com/D8CB)