

Picomag

Electromagnetic flowmeter

Smart magmeter for utilities – intuitive · convenient · multivariable



a partir de **R\$ 4.117,86**

Preço a partir de 05.08.2021

Mais informações e preço atual:

www.br.endress.com/DMA

Benefícios:

- Time-saving, easy configuration even in places difficult to reach – secure Bluetooth connection
- Fewer measuring points necessary – simultaneous flow, conductivity and temperature measurement
- Cost-efficient specialist for use in tight spaces e.g. skids – sensor and transmitter in one housing
- Quick offline configuration check – unique, comfortable knock functionality
- Simple device access through its whole lifecycle – no manual needed due to intuitive SmartBlue App
- Instant local process monitoring – large, user-friendly display of all measurement activities
- Flexible integration into all fieldbus systems – plug-and-play device with IO-Link

Especificações resumidas

- **Max. measurement error** Volume flow: +/-0.8% o.r. +/- 0.2% o.f.s
- **Measuring range** up to 750 l/min
- **Medium temperature range** -10 to 85 °C
- **Max. process pressure** 16 bar
- **Wetted materials** PEEK, Stainless Steel, FKM, EPDM Electrodes: 1.4404/316L

Campo de aplicação: Picomag is the economical magmeter for many applications in secondary circuits with conductive liquids in all industries. End customers, skid builders, equipment manufacturers and system integrators value the space-saving Picomag for its flexible installation

capabilities. Additionally, its future-oriented, intuitive operation via SmartBlue app on every Bluetooth-enabled smartphone or tablet ensures fast, secure and simple commissioning.

Características e especificações

Liquids

Measuring principle

Electromagnetic

Product headline

Smart magmeter for utilities – intuitive · convenient · multivariable. Time-saving, easy configuration even in places difficult to reach – secure Bluetooth connection.

Ideal for process quality control and monitoring due to temperature and conductivity measurement in utilities.

Sensor features

Fewer measuring points necessary – simultaneous flow, conductivity and temperature measurement. Cost-efficient specialist for use in tight spaces e.g. skids – sensor and transmitter in one housing.

High shock and vibration resistance. Degree of protection: IP65/67.

Empty pipe detection.

Transmitter features

Quick offline configuration check – unique, comfortable knock functionality. Simple device access through its whole lifecycle – no manual needed due to intuitive SmartBlue app. Effortless configuration of several devices – settings can be saved and loaded into other meters. Flexible integration into all fieldbus systems – plug-and-play device with IO-Link.

Wireless remote access via Bluetooth SmartBlue app. IO-Link and various I/Os for all line-sizes. 1.4" TFT color display with backlight.

Nominal diameter range

DN15 to 50 (1/2 to 2")

Liquids

Wetted materials

PEEK, Stainless Steel, FKM, EPDM

Electrodes: 1.4404/316L

Measured variables

Volume flow, Temperature, Conductivity

Max. measurement error

Volume flow: +/-0.8% o.r. +/- 0.2% o.f.s

Measuring range

up to 750 l/min

Max. process pressure

16 bar

Medium temperature range

-10 to 85 °C

Ambient temperature range

-10 to 60 °C

Sensor housing material

1.4404/316L, Polycarbonate

Transmitter housing material

1.4404/316L, Polycarbonate

Degree of protection

IP 65/67

Display/Operation

Integrated display, operation via SmartBlue app

Liquids

Outputs

Current (4 to 20mA)

Pulse

Switch

Voltage (2 to 10V)

Inputs

Status

Digital communication

IO-Link

Power supply

18 to 30V DC

Product safety

cULus listing

Hygienic approvals and certificates

Drinking water approvals: NSF

Mais informações www.br.endress.com/DMA