

Digital ORP sensor Memosens CPS42E

Memosens 2.0 ORP sensor for applications with fast-changing medium compositions or low conductivity



Mais informações e preço atual:

www.br.endress.com/CPS42E

Benefícios:

- Memosens 2.0 offers extended storage of calibration and process data, enabling better trend identification and providing a future-proof basis for predictive maintenance and enhanced IIoT services.
- Resistant to poisoning due to permanent refilling of KCl bridge electrolyte and separate reference lead
- Perfectly suited for quickly changing media: Combination of liquid KCl electrolyte and ceramic junction enables fast response time
- Applicable at very low conductivities ($> 5 \mu\text{S}/\text{cm}$) thanks to liquid KCl electrolyte
- Suitable for cleaning in place (CIP) and sterilization in place (SIP)
- Maximum process safety through non-contact inductive signal transmission
- Reduced operating costs due to minimized process downtime and extended sensor lifetime

Especificações resumidas

- **Measurement range** $-1\ 500$ to $1\ 500$ mV
- **Process temperature** -15 to 135 °C (5 to 275 °F)
- **Process pressure** 0.8 to 11 bar (11.6 to 159.5 psi) (absolute)

Campo de aplicação: Memosens CPS42E is the high performer for harsh chemical applications, media with low conductivity or considerable organic content. The sensor is designed for fast response especially in applications with fast-changing media. Thanks to Memosens 2.0 digital technology, CPS42E combines maximum process integrity with simple operation. It resists moisture and enables lab calibration. It offers

extended storage of calibration and process data providing the perfect basis for predictive maintenance.

Características e especificações

ORP / Redox

Measuring principle

Sensor ORP / Redox

Application

Media with very low conductivity or a high proportion of organic solvents or alcohol:

- Chemical industry
- Organic chemicals
- Power stations
- Laboratory measurements

Characteristic

Digital ORP electrode for process engineering with ceramic junction and KCl liquid electrolyte

Measurement range

-1 500 to 1 500 mV

Measuring principle

Liquid-KCl filling and ceramic junction

Design

All shaft lengths with temperature sensor

ORP / Redox

Material

Sensor shaft: Glass to suit process

ORP measuring element: Platinum

Metal lead: Ag/AgCl

Open aperture: Ceramic junction, zirconium dioxide

O-ring: FKM

Process coupling: PPS fiber-glass reinforced

Nameplate: Ceramic metal oxide

Dimension

Diameter: 12 mm (0.47 inch)

Shaft length: 120, 225, 360 and 425 mm
(4.72, 8.86, 14.17 and 16.73 inch)

Process temperature

-15 to 135 °C (5 to 275 °F)

Process pressure

0.8 to 11 bar (11.6 to 159.5 psi) (absolute)

Temperature sensor

NTC 30k

Ex certification

With ATEX, IECEx, CSA C/US, NEPSI, Japan Ex and INMETRO approvals for use in hazardous areas Zone 0, Zone 1 and Zone 2.

Connection

Inductive, contactless connection head with Memosens 2.0 technology

ORP / Redox

Ingres protection

IP68

Additional certifications

Additional certifications

Mais informações www.br.endress.com/CPS42E