

Micropilot M FMR245



Mais informações e preço atual:

www.br.endress.com/FMR245

Benefícios:

- Non-contact measurement: Measurement is almost independent from product properties
- 2-wire technology, low price: A real alternative to differential pressure, floats and displacers.
2-wire technology reduces wiring costs and allows easy implementation into existing systems
- Easy commissioning, documentation and diagnostics via Endress+Hauser operating software
- Easy on-site operation via menu-driven alphanumeric display
- Used for level monitoring (MIN, MAX) up to SIL 2 as per IEC 61508/IEC 61511-1
- HART or PROFIBUS PA respectively FOUNDATION Fieldbus protocol
- Option: Gastight feedthrough to improve the process safety

Especificações resumidas

- **Accuracy** +/- 3 mm
- **Process temperature** -40° C...+200° C (-40 °F...+392 °F)
- **Process pressure absolute / max. overpressure limit**
Vacuum...16 bar (Vacuum...232 psi)
- **Max. measurement distance** Max. measurement distance
- **Main wetted parts** PTFE

Campo de aplicação: The Micropilot FMR245 offers cost-effective 4 to 20mA 2-wire technology and is suitable for hazardous locations. The FMR245 is used for continuous, non-contact level measurement of liquids, pastes, slurries, and solids. The measurement is not affected by changing media, temperature changes, gas blankets or vapors.

Características e especificações

Continuous / Liquids**Measuring principle**

Level radar

Characteristic / Application

Characteristic / Application

Supply / Communication2-wire (HART / PROFIBUS PA / FOUNDATION
Fieldbus)**Frequency**

K-Band (~ 26 GHz)

Accuracy

+/- 3 mm

Ambient temperature-40 °C...+80 °C
(-40 °F...+176 °F)**Process temperature**-40 °C...+200 °C
(-40 °F...+392 °F)**Process pressure absolute / max. overpressure limit**Vacuum...16 bar
(Vacuum...232 psi)**Main wetted parts**

PTFE

Process connection

DN50...DN150

Process connection hygienicTri-Clamp ISO2852
DIN11851

Continuous / Liquids

Tamanho do tanque / aplicação

Tamanho do tanque / aplicação

Max. measurement distance

Max. measurement distance

Communication

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Certificates / Approvals

ATEX, FM, CSA, IECEx, TIIS, NEPSI

Overfill prevention WHG

SIL

EN 10204-3.1

Marine GL

3A, EHEDG

Application limits

Application limits

Mais informações www.br.endress.com/FMR245