

TMT142C

TC Thermometer, fieldtransmitter, display

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



Mais informações e preço atual:

www.br.endress.com/TMT142C

Benefícios:

- Dual compartment housing
- Backlit display with large measured value, bar graph and fault condition indication
- Galvanic isolation 2 kV (sensor input to the output)
- Wide range of threaded thermowell connections available as standard
- Replaceable measuring insert comprising a mineral insulated tube (SS 316L/1.4404)
- Approvals for hazardous areas: Flameproof enclosure (Ex d), Intrinsic safety (Ex ia), Non-sparking (Ex nA)
- Aluminum or stainless steel housing, degree of protection IP67, NEMA 4x

Especificações resumidas

- **Accuracy** class 1 acc. to IEC 60584 class 2 acc. to IEC 60584
- **Response time** depending on configuration $t_{50} = 3$ s $t_{90} = 7$ s
- **Max. process pressure (static)** depending on thermowell
- **Operating temperature range** Type K: -40 °C ... 800 °C (-40 °F ... 1.472 °F) Type J: -40 °C ... 750 °C (-40 °F ... 1.382 °F)
- **Max. immersion length on request** up to $30.000,00$ mm ($1.181,10$ ")

Campo de aplicação: The robust thermometer is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas and Energy industry. The thermometer fulfills the corresponding safety requirements due to various certificates and tests. The use of a

transmitter leads to higher accuracy and reliability in comparison to directly wired sensors.

Características e especificações

Thermometer

Measuring principle

Thermocouple

Characteristic / Application

US style
 modular temperature assembly
 for heavy duty applications
 suitable for hazardous areas
 threaded process connection
 to use with thermowell
 backlit display

Thermowell / protection tube

to use with thermowell

Insert / probe

mineral insulated (MI), flexible

Outer diameter protection tube / Insert

Not defined

Max. immersion length on request

up to 30.000,00 mm (1.181,10")

Material protection tube/ thermowell

Not defined

Optional coating

Not defined

Thermometer

Process connection

male thread:

G1/2"

NPT1/2"

NPT3/4"

union nut:

NPT1/2"

M24x1.5

Tip shape

straight

Operating temperature range

Type K:

-40 °C ...800 °C

(-40 °F ...1.472 °F)

Type J:

-40 °C ... 750 °C

(-40 °F ...1.382 °F)

Max. process pressure (static)

depending on thermowell

Accuracy

class 1 acc. to IEC 60584

class 2 acc. to IEC 60584

Response time

depending on configuration

t₅₀ = 3 st₉₀ = 7 s**Integration head transmitter**yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Thermometer

Ex - approvals

ATEX II

Explosion proof

Mais informações www.br.endress.com/TMT142C