

Digital combined pH/ORP sensor Memosens CPS16E

Memosens 2.0 glass electrode for standard applications in process and water & wastewater industries



Mais informações e preço atual:

www.br.endress.com/CPS16E

Benefícios:

- Memosens 2.0 offers extended storage of calibration and process data, enabling better trend identification and providing a future-proof basis for predictive maintenance and enhanced IIoT services.
- The additional platinum electrode enables constant monitoring of reference impedance and is a reliable indicator of the sensor quality.
- Simultaneous measurement of pH, ORP and rH values (in rH mode) offers a better process overview and allows for a tighter process control.
- Robust: Large PTFE ring junction and reference with ion trap prevent poisoning of the sensor.
- Suitable for harsh applications: Process glass for highly alkaline media and pressure-stable up to 17 bar (246 psi).
- Reduced operating costs: Lab calibration and fast sensor exchange on site minimize process downtime. Sensor regeneration in the laboratory extends the sensor lifetime.
- Non-contact, digital signal transmission ensures reliable measurements resulting in maximum process safety.

Especificações resumidas

- **Measurement range** ORP: -1 500 to 1 500 mV Application A ▪ pH: 1 to 12 Application B ▪ pH: 0 to 14
- **Process temperature** Application A: -15 to 80 °C (5 to 176 °F) Application B: 0 to 135 °C (32 to 275 °F)
- **Process pressure** 0.8 to 17 bar (11.6 to 246,5 psi) absolute

Campo de aplicação: Memosens CPS16E is suitable for simultaneous pH and ORP measurement in applications with long-term stable conditions. Thanks to its pH and ORP elements, the sensor offers a better process overview and enables tighter process control. Memosens CPS16E features Memosens 2.0 digital technology, offering extended data storage for predictive maintenance. The pH/ORP sensor resists moisture and enables lab calibration which makes the operator's daily tasks easier and maximizes process integrity.

Características e especificações

pH

Measuring principle

Potentiometric

Application

Long-term monitoring and limit control in processes with stable process conditions

- Chemical processes
- Pulp and paper industry
- Waste incinerators and gas scrubbers
- Mining
- Wastewater

Characteristic

Combination of pH and ORP electrode for standard applications in process technology and environmental engineering

Poison-resistant reference with ion trap

Measurement range

ORP: -1 500 to 1 500 mV

Application A

- pH: 1 to 12

Application B

- pH: 0 to 14

pH

Measuring principle

Gel compact electrode with PTFE ring-junction and with ion trap
Pt-disc as additional ORP element
rH measurement and control of the reference impedance

Design

All shaft lengths with temperature sensor
Advanced gel technology

Material

Sensor shaft: Glass to suit process
pH membrane glass: Type A, B
Metal lead: Ag/AgCl
Open aperture: PTFE junction, sterilizable
ORP measuring element: Platinum
O-ring: FKM
Process coupling: PPS fiber-glass reinforced
Nameplate: Ceramic metal oxide

Dimension

Diameter: 12 mm (0.47 inch)
Shaft lengths: 120, 225 and 360 mm
(4.72, 8.86, 14.17 and 16.73 inch)

Process temperature

Application A: -15 to 80 °C (5 to 176 °F)
Application B: 0 to 135 °C (32 to 275 °F)

Process pressure

0.8 to 17 bar (11.6 to 246,5 psi) absolute

Temperature sensor

NTC 30k

Ex certification

With ATEX, IECEx, CSA C/US, NEPSI, Japan Ex and INMETRO approvals
for use in
hazardous areas Zone 0, Zone 1 and Zone 2

pH

Connection

Inductive, digital connection head with Memosens 2.0 technology

Ingres protection

IP68

ORP / Redox

Measuring principle

Sensor ORP / Redox

Application

Long-term monitoring and limit control in processes with stable process conditions

Chemical processes

- Pulp and paper industry
 - Waste incinerators and gas scrubbers
 - Mining
 - Wastewater
-

Characteristic

Combination of pH and ORP electrode for standard applications in process technology and environmental engineering

Poison-resistant reference with ion trap

Measurement range

ORP: -1 500 ... 1 500 mV

Application: A

- pH: 1 to 12

Application B

- pH: 0 to 14
-

Measuring principle

Gel compact electrode with PTFE ring-junction with ion trap

Pt-disc as additional ORP element

rH measurement and control of the reference impedance

ORP / Redox

Design

All shaft lengths with temperature sensor
Advanced gel technology

Material

Sensor shaft: Glass to suit process
pH membrane glass: Type A, B
Metal lead: Ag/AgCl
Open aperture: PTFE junction, sterilizable
ORP measuring element: Platinum
O-ring: FKM
Process coupling: PPS fiber-glass reinforced
Nameplate: Ceramic metal oxide

Dimension

Diameter: 12 mm (0.47 inch)
Shaft lengths: 120, 225 and 360 mm
(4.72, 8.86, 14.17 and 16.73 inch)

Process temperature

Application A: -15 to 80 °C (5 to 176 °F)
Application B: 0 to 135 °C (32 to 275 °F)

Process pressure

0.8 to 17 bar (11.6 to 246,5 psi) absolute

Temperature sensor

NTK 30k

Ex certification

With ATEX, IECEx, CSA C/US, NEPSI, Japan Ex and INMETRO approvals
for use in
hazardous areas Zone 0, Zone 1 and Zone 2

Connection

Inductive, digital connection head with Memosens 2.0 technology

Ingres protection

IP68

ORP / Redox

Mais informações www.br.endress.com/CPS16E