

4-channel transmitter Liquiline CM444R

Expandable multiparameter DIN-rail and cabinet device for all industries



Mais informações e preço atual:

www.br.endress.com/CM444R

Benefícios:

- **Saves space, saves money:**
Small footprint, 4 channels in one device, expandable at any time, saves space in cabinets – perfect for skids.
- **High-speed installation:**
No cut-out in cabinet door, one-click DIN-rail mounting, minimized wiring.
- **Simple and safe commissioning:**
Saving configuration on SD card enables fast set-up on duplicate installations.
- **Easy to operate and service:**
Intuitive user interface, hot plug & play with pre-calibrated Memosens sensors, universal components fit all parameters.
- **Process control from a distance:**
Integrated web server that allows the operator to remotely view diagnostic data, perform configurations, or access device parameters in any web browser - even via Smartphone.
- **Higher availability, lower costs:**
Heartbeat Technology enables status-oriented maintenance and easy verification of the entire measuring point and helps to carry out optimization measures.

Especificações resumidas

- **Input** 1 to 4x Memosens digital input 2x 0/4 to 20mA Input optional 2 to 4x Digital input optional
- **Output / communication** 2 to 8x 0/4 to 20 mA current outputs, alarmrelay, 4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

- **Ingres protection** Transmitter: IP20 Optional Display: IP66

Campo de aplicação: Liquiline CM444R is a digital multiparameter transmitter for process monitoring and control in all applications - even where mounting space is limited. You save time and money through fast and simple installation, operation and handling. The 4-channel controller can be extended to accommodate up to 8 sensors at any time to fit the needs of your process. Liquiline CM444R provides you with all the benefits of a best-in-class transmitter platform from clever simplicity to maximum process safety.

Características e especificações

Conductivity

Measuring principle

Potentiometric

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output

Alarmrelay, 4x relay, SD card for software update and copy & paste of setup

Material

DIN rail housing: PC-FR

Display seal: EPDM

Conductivity

Dimension

220 x 100 x 97 mm

8.66 x 3.94 x 3.82 inch

Process temperature0 to 55 °C (32 to 130 °F)

Ingres protection

Transmitter: IP20

Optional Display: IP66

Input

1 to 4x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certificationsEAC, cCSAus

Sludge Level

Measuring principleUltrasonic sensor

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Sludge Level

Characteristic

Robust plastic housing
All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output,
Alarmrelay, 4x relay, SD card for software update and copy & paste of
setup

Material

DIN rail housing: PC-FR
Display seal: EPDM

Dimension

220 x 100 x 97 mm
8.66 x 3.94 x 3.82 inch

Process temperature

0 to 55 °C (32 to 130 °F)

Ingres protection

Transmitter: IP20
Optional Display: IP66

Input

1 to 4x Memosens digital input
2x 0/4 to 20mA Input optional
2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

ORP / Redox

Measuring principle

Sensor ORP / Redox

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output

Alarmrelay, 4x relay, SD card for software update and copy & paste of setup

Material

DIN rail housing: PC-FR

Display seal: EPDM

Dimension

220 x 100 x 97 mm

8.66 x 3.94 x 3.82 inch

Process temperature

0 to 55 °C (32 to 130 °F)

Ingres protection

Transmitter: IP20

Optional Display: IP66

ORP / Redox**Input**

1 to 4x Memosens digital input
2x 0/4 to 20mA Input optional
2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

pH**Measuring principle**

Potentiometric

Application

Modular 4 wire controller
Multichannel: 1 to 4 digital channels for Memosens protocol
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive,
dissolved oxygen, nitrate and turbidity
4 sensors connectable in any combination
Functionality modular extendable at any time
Plug and play for modules and sensors

Characteristic

Robust plastic housing
All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output,
Alarmrelay, 4x relay, SD card for software update and copy & paste of
setup

Material

DIN rail housing: PC-FR
Display seal: EPDM

pH

Dimension

220 x 100 x 97 mm

8.66 x 3.94 x 3.82 inch

Process temperature

0 to 55 °C (32 to 130 °F)

Ingres protection

Transmitter: IP20

Optional Display: IP66

Input

1 to 4x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Disinfection

Measuring principle

Total chlorine

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Disinfection

Characteristic

Robust plastic housing
All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output,
Alarmrelay, 4x relay, SD card for software update and copy & paste of
setup

Material

DIN rail housing: PC-FR
Display seal: EPDM

Dimension

220 x 100 x 97 mm
8.66 x 3.94 x 3.82 inch

Process temperature

0 to 55 °C (32 to 130 °F)

Input

1 to 4x Memosens digital input
2x 0/4 to 20mA Input optional
2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Turbidity

Measuring principle

Single beam scattered light

Turbidity

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output,

Alarmrelay, 4x relay, SD card for software update and copy & paste of setup

Material

DIN rail housing: PC-FR

Display seal: EPDM

Dimension

220 x 100 x 97 mm

8.66 x 3.94 x 3.82 inch

Process temperature

0 to 55 °C (32 to 130 °F)

Ingres protection

Transmitter: IP20

Optional Display: IP66

Input

1 to 4x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Turbidity

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Oxygen

Measuring principle

Amperometric oxygen measurement

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive,
dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output,

Alarmrelay, 4x relay, SD card for software update and copy & paste of
setup

Material

DIN rail housing: PC-FR

Display seal: EPDM

Dimension

220 x 100 x 97 mm

8.66 x 3.94 x 3.82 inch

Oxygen

Process temperature

0 to 55 °C (32 to 130 °F)

Input

1 to 4x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Mais informações www.br.endress.com/CM444R