

iTHERM TMS01 MultiSens Flex Multipoint

Modular direct contact TC and RTD multipoint thermometer for oil, gas and petrochemical applications



Mais informações e preço atual:

www.br.endress.com/TMS01

Benefícios:

- Easy-to-use device with modular and flexible design, ready to be installed either for direct contact measurements or by means of sensor-dedicated protecting tubes. The device can also be installed in thermowells already in place
- Infinite layouts of 3D sensors distribution for any desired process monitoring configuration
- High degree of customization thanks to a modular product design for easy installation, process integration and maintenance
- High degree of insert process compatibility as per standard IEC 60584, ASTM E230 and IEC 60751
- On-board electronic heat protection for highest product durability
- Compliance to different types of protection for use in hazardous locations for easy process integration

Especificações resumidas

- **Accuracy** class 2 acc. to IEC 60584 ASTM E230 and ANSI MC 96.1
- **Response time** depending on configuration: TC: t50 = 2 s t90 = 5 s RTD: t50 = 0,8s t90 = 2s
- **Max. process pressure (static)** at 20 °C: 100 bar (1450 psi)
- **Operating temperature range** Type K: -270 °C ...1.100 °C (-454 °F ...2.012 °F) Type J: -210 °C ...760 °C (-346 °F ...1.382 °F) Type N: -270 °C ...1100 °C (-454 °F ...2.012 °F) Type T: -270 °C ...370 °C (-454 °F ...698 °F)
- **Max. immersion length on request** up to 30.000,00 mm (1181")

Campo de aplicação: By complying with the highest safety standards, iTHERM TMS01 can be customized for various applications. Bendable into a 3D layout, it provides a complete temperature profile just by using one nozzle. The device is configurable with or without thermowells for optimal response times, mechanical strength or sensors replaceability. It is available either with TC or RTD technology or with our iTHERM StrongSens.

Características e especificações

Thermometer

Measuring principle

Resistance Temperature Detector

Characteristic / Application

metric style

easy-to-use

suitable for hazardous areas

flanged process connection

light chemical processes

3D sensors distributions

modular design

replaceable sensors during shutdown

Thermometer**Thermowell / protection tube**

without (for direct contact sensors type)

with (for replaceable sensors)

with (for increased mechanical protection)

Multi-thermowells, each one dedicated to a sensor

Insert / probe

mineral insulated (MI), flexible

mineral insulated (MI), flexible, with its own thermowell

Outer diameter protection tube / Insert

6,0 mm (0,24")

8,0 mm (0,31")

10,29 mm (1/8")

Max. immersion length on request

up to 30.000,00 mm (1181")

Material protection tube/ thermowell

1.4401 (316)

1.4435 (316L)

1.4541 (321)

1.4550 (347)

Alloy 600 (2.4816)

Thermometer**Process connection**

flange:

2" ASME/ANSI B16.5 150
...6003" ASME/ANSI B16.5 150
..6004" ASME/ANSI B16.5 150
...6006" ASME/ANSI B16.5 150
...6008" ASME/ANSI B16.5 150
...600DN80 EN/DIN 1092.1 PN10
...PN100DN100 EN/DIN 1092.1 PN10
...PN100DN125 EN/DIN 1092.1 PN10
...PN100DN150 EN/DIN 1092.1 PN10
...PN100DN200 EN/DIN 1092.1 PN10
...PN100

Tip shapestraight

Thermometer

Operating temperature range

Type K:

-270 °C ...1.100 °C

(-454 °F ...2.012 °F)

Type J:

-210 °C ...760 °C

(-346 °F ...1.382 °F)

Type N:

-270 °C ...1100 °C

(-454 °F ...2.012 °F)

Type T:

-270 °C ...370 °C

(-454 °F ...698 °F)

Max. process pressure (static)at 20 °C: 100 bar (1450 psi)

Accuracy

class 2 acc. to IEC 60584

ASTM E230 and ANSI MC 96.1

Thermometer**Response time**

depending on configuration:

TC:

t50 = 2 s

t90 = 5 s

RTD:

t50 = 0,8s

t90 = 2s

Integration head transmitteryes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Ex - approvals

ATEX

IECEX

Certification

SIL (transmitter only)

Mais informações www.br.endress.com/TMS01