

Digital ammonium and nitrate sensor ISEmax CAS40D

Ion-selective Memosens sensor for the wastewater industry



Mais informações e preço atual:

www.br.endress.com/CAS40D

Benefícios:

- Nitrate and ammonium measured directly without the need for expensive sample conditioning
- Optional potassium and/or chloride measurement compensates for cross sensitivities and ensures reliable measuring results
- Low maintenance thanks to automatic flushing unit
- Installed directly on the basin rim, no measuring container or sample-conveying pump required
- Easy handling due to storage of sensor-specific data

Especificações resumidas

- **Measurement range** Ammonium: 0.1 to 1000 mg/l (NH₄-N)
Nitrate: 0.1 to 1000 mg/l (NO₃-N) Potassium: 1 to 1000 mg/l
Chloride: 1 to 1000 mg/l
- **Process temperature** 2 °C to 40°C (36 to 100 °F)
- **Process pressure** 400 mbar (160 in H₂O) max. permitted overpressure

Campo de aplicação: ISEmax CAS40D is the right technology for trend measurement directly in the basin. It helps you to increase the efficiency and reduce the energy costs of your aeration processes. The sensor works without reagents saving you even further money. With its robust ion-selective membranes and excellent self-cleaning, it eases your maintenance tasks. Thanks to Memosens, CAS40D combines maximum process and data integrity with best operating comfort and simplifies predictive maintenance.

Características e especificações

Analyser

Measuring principle

Potentiometric / ISE

Characteristic

Online measurement of nutrient parameters in municipal wastewater treatment plants

Ion-selective electrode system for the continuous measurement of ammonium and nitrate

Size

Diameter: 112 mm (4.41 inch)

Immersion depth: 510mm (20.08 inch)

Design

Ion-selective electrode(s) for ammonium and/or nitrate, potassium or chloride

pH - (Reference) electrode

Ion-selective electrode for compensating cross-interference

Temperature sensor

Process temperature

2 °C to 40°C (36 to 100 °F)

Ambient temperature

-20 °C to 50 °C (-4 to 120 °F)

Process pressure

400 mbar (160 in H₂O) max. permitted overpressure

Application

Wastewater treatment plants

Analyser**Measurement range**

Ammonium:

0.1 to 1000 mg/l (NH₄-N)

Nitrate:

0.1 to 1000 mg/l (NO₃-N)

Potassium:

1 to 1000 mg/l

Chloride:

1 to 1000 mg/l

Mais informações www.br.endress.com/CAS40D