

# Proline Cubemass C 100 Coriolis flowmeter

Compact sensor for smallest quantities with  
an ultra-compact transmitter



More information and current pricing:

[www.ca.endress.com/8C1B](http://www.ca.endress.com/8C1B)

## Benefits:

- Space-saving installation – compact single-tube design
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Suitable for skids – lightweight sensor
- Space-saving transmitter – full functionality on the smallest footprint
- Time-saving local operation without additional software and hardware – integrated web server
- Integrated verification – Heartbeat Technology

## Specs at a glance

- **Max. measurement error** Mass flow (liquid):  $\pm 0.1\%$  Volume flow (liquid):  $\pm 0.1\%$  Mass flow (gas):  $\pm 0.5\%$  Density (liquid):  $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 1000 kg/h (0 to 37 lb/min)
- **Medium temperature range**  $-50$  to  $+205 \text{ }^\circ\text{C}$  ( $-58$  to  $+401 \text{ }^\circ\text{F}$ )
- **Max. process pressure** PN 40, Class 300, 10K, 400 bar (5800 psi)
- **Wetted materials** Measuring tube: 1.4539 (904L) Connection: 1.4539 (904L); 1.4404 (316/316L)

**Field of application:** Cubemass C is the ideal sensor for the measurement of smallest flow rates in skids, test rigs and industrial robotics. Neither high pressure nor alternating flow conditions compromise its accuracy. The ultra-compact transmitter delivers full performance on the smallest footprint and enables seamless system integration. Heartbeat Technology ensures measurement reliability and compliant verification.

## Features and specifications

## Liquids

### Measuring principle

Coriolis

---

### Product headline

Compact sensor for smallest quantities with an ultra-compact transmitter.

Measuring accurately smallest quantities of liquids and gases.

---

### Sensor features

Space-saving installation – compact single-tube design. Fewer process measuring points – multivariable measurement (flow, density, temperature). Suitable for skids – lightweight sensor.

Nominal diameter: DN 1 to 6 ( $\frac{1}{24}$  to  $\frac{1}{4}$ " ). Process pressure up to 400 bar (5800 psi). Medium temperature up to +205 °C (+401 °F).

---

### Transmitter features

Space - saving transmitter – full functionality on the smallest footprint. Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra-compact transmitter housing. Pre - configured plug connector. Local display available.

---

### Nominal diameter range

DN 1 to 6 ( $\frac{1}{24}$  to  $\frac{1}{4}$ " )

---

### Wetted materials

Measuring tube: 1.4539 (904L)

Connection: 1.4539 (904L); 1.4404 (316/316L)

---

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

---

### Max. measurement error

Mass flow (liquid):  $\pm 0.1$  %

Volume flow (liquid):  $\pm 0.1$  %

Mass flow (gas):  $\pm 0.5$  %

Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

---

---

## Liquids

**Measuring range**

0 to 1000 kg/h (0 to 37 lb/min)

---

**Max. process pressure**

PN 40, Class 300, 10K, 400 bar (5800 psi)

---

**Medium temperature range**

-50 to +205 °C (-58 to +401 °F)

---

**Ambient temperature range**

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

---

**Sensor housing material**

1.4301 (304), corrosion resistant

---

**Transmitter housing material**

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304)

---

**Degree of protection**

Standard: IP66/67, type 4X enclosure

---

**Display/Operation**

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

---

**Outputs**

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

---

**Inputs**

None

---

**Digital communication**

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

---

**Power supply**

DC 20 to 30 V

---

---

## Liquids

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI

---

**Product safety**

CE, C-Tick

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

CRN

---

**Material certificates**

3.1 material

---

## Density/Concentration

**Measuring principle**

Coriolis

---

**Product headline**

Compact sensor for smallest quantities with an ultra-compact transmitter.

Measuring accurately smallest quantities of liquids and gases.

---

**Sensor features**

Space-saving installation – compact single-tube design. Fewer process measuring points – multivariable measurement (flow, density, temperature). Suitable for skids – lightweight sensor.

Nominal diameter: DN 1 to 6 ( $\frac{1}{2}$ " to  $\frac{1}{4}$ "). Process pressure up to 400 bar (5800 psi). Medium temperature up to +205 °C (+401 °F).

---

## Density/Concentration

### Transmitter features

Space - saving transmitter – full functionality on the smallest footprint.  
Time - saving local operation without additional software and hardware  
– integrated web server. Integrated verification – Heartbeat Technology.  
Robust, ultra-compact transmitter housing. Pre - configured plug  
connector. Local display available.

---

### Nominal diameter range

DN 1 to 6 ( $\frac{1}{24}$  to  $\frac{1}{4}$ " )

---

### Wetted materials

Measuring tube: 1.4539 (904L)

Connection: 1.4539 (904L); 1.4404 (316/316L)

---

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow,  
reference density, concentration

---

### Max. measurement error

Mass flow (liquid):  $\pm 0.1$  %

Volume flow (liquid):  $\pm 0.1$  %

Mass flow (gas):  $\pm 0.5$  %

Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

---

### Measuring range

0 to 1000 kg/h (0 to 37 lb/min)

---

### Max. process pressure

PN 40, Class 300, 10K, 400 bar (5800 psi)

---

### Medium temperature range

-50 to +205 °C (-58 to +401 °F)

---

### Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

---

### Sensor housing material

1.4301 (304), corrosion resistant

---

## Density/Concentration

---

### Transmitter housing material

Compact: AlSi10Mg, coated  
Compact/ultra - compact: 1.4301 (304)

---

### Degree of protection

Standard: IP66/67, type 4X enclosure

---

### Display/Operation

4 - line backlit display available (no local operation)  
Configuration via web browser and operating tools possible

---

### Outputs

4 - 20 mA HART (active)  
Pulse/frequency/switch output (passive)

---

### Inputs

None

---

### Digital communication

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

---

### Power supply

DC 20 to 30 V

---

### Hazardous area approvals

ATEX, IECEx, cCSAus, INMETRO, NEPSI

---

### Product safety

CE, C-Tick

---

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)  
Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

### Pressure approvals and certificates

CRN

---

---

**Density/Concentration****Material certificates**

3.1 material

---

**Gas****Measuring principle**

Coriolis

---

**Product headline**

Compact sensor for smallest quantities with an ultra-compact transmitter.

Measuring accurately smallest quantities of liquids and gases.

---

**Sensor features**

Space-saving installation – compact single-tube design. Fewer process measuring points – multivariable measurement (flow, density, temperature). Suitable for skids – lightweight sensor.

Nominal diameter: DN 1 to 6 ( $\frac{1}{24}$  to  $\frac{1}{4}$ "). Process pressure up to 400 bar (5800 psi). Medium temperature up to +205 °C (+401 °F).

---

**Transmitter features**

Space - saving transmitter – full functionality on the smallest footprint. Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra-compact transmitter housing. Pre - configured plug connector. Local display available.

---

**Nominal diameter range**

DN 1 to 6 ( $\frac{1}{24}$  to  $\frac{1}{4}$ ")

---

**Wetted materials**

Measuring tube: 1.4539 (904L)

Connection: 1.4539 (904L); 1.4404 (316/316L)

---

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

---

## Gas

**Max. measurement error**Mass flow (liquid):  $\pm 0.1$  %Volume flow (liquid):  $\pm 0.1$  %Mass flow (gas):  $\pm 0.5$  %Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>**Measuring range**

0 to 1000 kg/h (0 to 37 lb/min)

**Max. process pressure**

PN 40, Class 300, 10K, 400 bar (5800 psi)

**Medium temperature range**

-50 to +205 °C (-58 to +401 °F)

**Ambient temperature range**

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

**Sensor housing material**

1.4301 (304), corrosion resistant

**Transmitter housing material**

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304)

**Degree of protection**

Standard: IP66/67, type 4X enclosure

**Display/Operation**

4 - line backlit display available (no local operation)

Configuration via web browser and operating Tools possible

**Outputs**

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

**Inputs**

None



Gas

**Digital communication**

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

---

**Power supply**

DC 20 to 30 V

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

CRN

---

**Material certificates**

3.1 material

---

More information [www.ca.endress.com/8C1B](http://www.ca.endress.com/8C1B)