

# Microwave barrier transmitter

## Soliwave FQR56

### Transmitter for non-contact point level detection in bulk solids



More information and current pricing:

[www.ca.endress.com/FQR56](http://www.ca.endress.com/FQR56)

#### Benefits:

- Highly reliable measurement due to flush-mounted installation and possible non-contact installation as well as indication of the signal strength on the receiver
- Mechanical robust solution ensures cost savings over the whole life cycle of the product: No wear and tear, process-wetted ceramic sensor diaphragm (optional), long serviceable life, maintenance free
- Electronics housing can be rotated by 360°, allowing adjustment into optimum position after installation
- Direct connection of the supply voltage (transmitter and receiver separately or together)
- Mechanically compatible to FQR50/FDR50 microwave barrier, existing process connections can continue to be used; likewise, accessories such as adapter flanges, installation brackets and sight glasses can continue to be used

#### Specs at a glance

- **Process temperature** Non-contact installation: any Within installation: -40 °C...+70 °C (-40 °F...+158 °F) With HT-Adapter: up to +450 °C (+842 °F)
- **Process pressure / max. overpressure limit** Non-contact installation: any Within installation: 0.5 bar...6.8 bar (7.2 psi...99 psi) abs. With HD-Adapter: up to +21 bar (+305 psi) abs.
- **Min. density of medium** Solid weight: > 10 g/l

**Field of application:** The Soliwave FQR56 microwave barrier uses a contact-free procedure for detection of point levels. It can be installed in containers, conduits, shafts or on free fall shafts. It is possible to take a measurement through non-metallic container materials from the

outside. Suitable as point level switch for controlling and counting all types of bulk solids. It interacts with the Soliwave FDR56 receiver.

## Features and specifications

### Point Level / Solids

#### Measuring principle

Microwave barrier

#### Characteristic / Application

Transmitter

Non-contact point level detection and flow monitoring

Detecting, counting and positioning of objects

Monitoring of material transfer points

Detection and analysis of deposits and contamination

Installation:

Non-contact installation (transmission window) or front-flush installation (contact)

#### Specialities

Measurement range: max. 100 m

#### Supply / Communication

85 ... 253VAC

20 ... 30 VDC/ 20 ... 60 VAC

#### Ambient temperature

-40 °C...+70 °C

(-40 °F...+158 °F)

#### Process temperature

Non-contact installation: any

Within installation:

-40 °C...+70 °C (-40 °F...+158 °F)

With HT-Adapter:

up to +450 °C (+842 °F)

---

## Point Level / Solids

### Process pressure / max. overpressure limit

Non-contact installation: any  
Within installation:  
0.5 bar...6.8 bar (7.2 psi...99 psi) abs.  
With HD-Adapter:  
up to +21 bar (+305 psi) abs.

---

### Min. density of medium

Solid weight: > 10 g/l

---

### Main wetted parts

Non-contact installation:  
no wetted parts  
Within installation:  
316Ti or Aluminium;  
PTFE or Ceramic

---

### Process connection

1-1/2" R, 1-1/2" G, 1-1/2" NPT

---

### Process connection hygienic

Non-contact installation

---

### Certificates / Approvals

ATEX, IEC Ex, CSA C/US

---

### Design approvals

EN10204-3.1

---

### Options

Sight glass  
High temperature adapter  
High pressure adapter  
Installation bracket  
FAR50, FAR51, FAR52, FAR53, FAR54, FAR55

---

### Components

Transceiver: FDR56

---

Point Level / Solids

**Application limits**

Solid weight: < 10 g/l

---

More information [www.ca.endress.com/FQR56](http://www.ca.endress.com/FQR56)