

# Digital ORP sensor Ceragel CPS72D

## Memosens glass electrode for the chemical and life sciences industries



More information and current pricing:

[www.ca.endress.com/CPS72D](http://www.ca.endress.com/CPS72D)

### Benefits:

- Sensor resists strong acids and bases and high organic loads
- Suitable for CIP/SIP and autoclaving maintaining high accuracy
- Free from animal-based materials and from acrylamide
- Maximum process safety through non-contact inductive signal transmission
- Enables predictive maintenance due to storage of sensor and process-specific data
- Reduced operating costs thanks to minimized process downtime and extended sensor lifetime

### Specs at a glance

- **Measurement range** -1500mV - +1500mV
- **Process temperature** -15°C - 140°C
- **Process pressure** max. 16bar

**Field of application:** Ceragel CPS72D is the digital specialist for demanding processes and hygienic applications. Its contamination-resistant gel guarantees stable measurement even in flowing media or low conductivity. The sensor measures reliably at high temperatures and is non-toxic assuring highest safety. Ceragel CPS72D is not the latest Memosens generation. To get information on the new Memosens CPS72E sensor with extended functionality, click [here](#).

### Features and specifications

## ORP / Redox

**Measuring principle**

Sensor ORP / Redox

---

**Application**

- Hygiene and sterile applications.- Pharmaceuticals, biotechnology, fermenters, contaminating media.

---

**Characteristic**

- Digital electrode with Memosens-Technology.- Gel-compact-electrode with ceramic diaphragm.- Platinum-cap- CIP/SIP and autoclavable- high accuracy

---

**Measurement range**

-1500mV - +1500mV

---

**Measuring principle**

- ceramic diaphragm- double chamber and double gel reference- Platinum-ring

---

**Dimension**

Diameter : 12mm Shaft length : 120,225,360mm

---

**Process temperature**

-15°C - 140°C

---

**Process pressure**

max. 16bar

---

**Ex certification**

ATEX

FM

CSA

---

**Connection**

Inductive transmission of digital measuring signals.

---

**Ingres protection**

IP68

---

ORP / Redox

**Additional certifications**

EHEDG

---

More information [www.ca.endress.com/CPS72D](http://www.ca.endress.com/CPS72D)