

Memosens CPS77D



More information and current pricing:

www.ca.endress.com/CPS77D

Benefits:

- Unbreakable for highest product safety
- Certified biocompatibility
- Suitable for hot steam sterilization and autoclaving
- Low maintenance thanks to long calibration intervals
- Six times higher CIP stability compared to conventional ISFET pH sensors
- Optional Pharma CoC available
- Maximum process safety through non-contact inductive signal transmission

Specs at a glance

- **Measurement range** pH 0 to 14
- **Process temperature** -15 to 135°C (5 to 275°F)
- **Process pressure** Max. 11 bar abs at 100 °C (Max. 160 psi at 212 °F)

Field of application: Memosens CPS77D is the digital specialist for hygienic applications. Its bacteria-proof reference with contamination-resistant gel guarantees stable measurements. The sensor is sterilizable with hot steam, autoclavable and features an unbreakable PEEK shaft assuring highest product safety. **Memosens CPS77D is not the latest Memosens generation. To get information on the new Memosens CPS77E sensor with extended functionality, click [here](#).**

Features and specifications

pH

Measuring principle

ISFET

pH

Application

Hygienic and sterile applications, food industry, pharmaceutical industry, biotechnology

Characteristic

Sterilizable and autoclavable ISFET sensor for pH measurement
Digital with Memosens technology

Reference

Double chamber reference system

Measurement range

pH 0 to 14

Material

Sensor shaft: PEEK
Seals: FFKM
Junction: ceramic

Dimension

Diameter: 12 mm (0.47 inch)
Shaft lengths: 120, 225 and 360 mm
(4.72, 8.86 and 14.2 inch)

Process temperature

-15 to 135°C (5 to 275°F)

Process pressure

Max. 11 bar abs at 100 °C
(Max. 160 psi at 212 °F)

Temperature sensor

Pt1000

Connection

Inductive, digital connection head with Memosens technology

Ingres protection

IP 68 (10 m (33 ft) water column, 25 °C (77 °F), 45 days)

pH

Additional certifications

3-A, FDA compatible

EHEDG Typ EL Class I aseptic

ASME BPE-2018

Regulation (EC) No. 1935/2004

USP <87>, USP <88> Class VI, 121 °C (250 °F)

More information www.ca.endress.com/CPS77D