

# Proline Promass E 300 Coriolis flowmeter

Mid-range Coriolis flowmeter with a compact, easily accessible transmitter



More information and current pricing:

[www.casc.endress.com/8E3B](http://www.casc.endress.com/8E3B)

## Benefits:

- Cost-effective – multipurpose device; an alternative to conventional volumetric flowmeters
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in-/outlet run needs
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

## Specs at a glance

- **Max. measurement error** Mass flow (liquid):  $\pm 0.15\%$  (standard),  $\pm 0.10\%$  (option) Volume flow (liquid):  $\pm 0.15\%$  Mass flow (gas):  $\pm 0.50\%$  Density (liquid):  $\pm 0.0005\text{ g/cm}^3$
- **Measuring range** 0 to 180 000 kg/h (0 to 6615 lb/min)
- **Medium temperature range**  $-40$  to  $+150\text{ }^\circ\text{C}$  ( $-40$  to  $+302\text{ }^\circ\text{F}$ )
- **Max. process pressure** PN 100, Class 600, 63K
- **Wetted materials** Measuring tube: 1.4539 (904L) Connection: 1.4404 (316/316L)

**Field of application:** The robust Promass E has a long-standing reputation as a reliable solution accurately measuring liquids and gases in a wide range of standard applications in various industries. With its compact transmitter Promass E 300 offers high flexibility in terms of operation and system integration: access from one side, remote display, improved connectivity options. Heartbeat Technology ensures measurement reliability and enables extension of recalibration cycles.

---

## Features and specifications

---

### Liquids

**Measuring principle**

Coriolis

---

**Product headline**

Flowmeter with minimized total cost of ownership and a compact, easily accessible transmitter.

Accurate measurement of liquids and gases for a wide range of standard applications.

---

**Sensor features**

Cost-effective – multi-purpose device; an alternative to conventional volumetric flowmeters. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs.

Compact dual-tube sensor. Medium temperature up to +150 °C (+302 °F).

---

**Transmitter features**

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Process pressure up to 100 bar (1450 psi). Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

---

**Nominal diameter range**

DN 8 to 80 (3/8 to 3")

---

**Wetted materials**

Measuring tube: 1.4539 (904L)

Connection: 1.4404 (316/316L)

---

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

---

## Liquids

**Max. measurement error**

Mass flow (liquid):  $\pm 0.15$  % (standard),  $\pm 0.10$  % (option)

Volume flow (liquid):  $\pm 0.15$  %

Mass flow (gas):  $\pm 0.50$  %

Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

---

**Measuring range**

0 to 180 000 kg/h (0 to 6615 lb/min)

---

**Max. process pressure**

PN 100, Class 600, 63K

---

**Medium temperature range**

-40 to +150 °C (-40 to +302 °F)

---

**Ambient temperature range**

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

---

**Sensor housing material**

1.4301 (304), corrosion resistant

---

**Transmitter housing material**

AlSi10Mg, coated; stainless steel for hygienic transmitter design

---

**Degree of protection**

Standard: IP66/67, Type 4X enclosure

IP69

---

**Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available"

---

## Liquids

### Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

---

### Inputs

Status input

4-20 mA input

---

### Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

---

### Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

---

### Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

---

### Product safety

CE, C-tick, EAC marking

---

### Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

---

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

## Liquids

### **Marine approvals and certificates**

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

---

### **Pressure approvals and certificates**

PED, CRN

---

### **Material certificates**

3.1 material

---

### **Hygienic approvals and certificates**

3-A, EHEDG, cGMP

---

## Gas

### **Measuring principle**

Coriolis

---

### **Product headline**

Flowmeter with minimized total cost of ownership and a compact, easily accessible transmitter.

Accurate measurement of liquids and gases for a wide range of standard applications.

---

### **Sensor features**

Cost-effective – multi-purpose device; an alternative to conventional volumetric flowmeters. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs.

Compact dual-tube sensor. Medium temperature up to +150 °C (+302 °F).

---

### **Transmitter features**

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Process pressure up to 100 bar (1450 psi). Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

## Gas

**Nominal diameter range**DN 8 to 80 ( $\frac{3}{8}$  to 3")**Wetted materials**

Measuring tube: 1.4539 (904L)

Connection: 1.4404 (316/316L)

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

**Max. measurement error**Mass flow (liquid):  $\pm 0.15$  % (standard),  $\pm 0.10$  % (option)Volume flow (liquid):  $\pm 0.15$  %Mass flow (gas):  $\pm 0.50$  %Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>**Measuring range**

0 to 180 000 kg/h (0 to 6615 lb/min)

**Max. process pressure**

PN 100, Class 600, 63K

**Medium temperature range**

-40 to +150 °C (-40 to +302 °F)

**Ambient temperature range**

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

**Sensor housing material**

1.4301 (304), corrosion resistant

**Transmitter housing material**

AlSi10Mg, coated; stainless steel for hygienic transmitter design

**Degree of protection**

Standard: IP66/67, Type 4X enclosure

IP69

## Gas

**Display/Operation**

4-line backlit display with touch control (operation from outside)  
Configuration via local display and operating tools possible  
Remote display available"

**Outputs**

3 outputs:  
4-20 mA HART (active/passive)  
4-20 mA WirelessHART  
4-20 mA (active/passive)  
Pulse/frequency/switch output (active/passive)  
Double pulse output (active/passive)  
Relay output

**Inputs**

Status input  
4-20 mA input

**Digital communication**

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus  
RS485, Profinet, Ethernet/IP, OPC-UA

**Power supply**

DC 24 V  
AC 100 to 230 V  
AC 100 to 230 V / DC 24 V (non-hazardous area)

**Hazardous area approvals**

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

**Product safety**

CE, C-tick, EAC marking

**Functional safety**

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

---

**Gas****Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Marine approvals and certificates**

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

---

**Pressure approvals and certificates**

PED, CRN

---

**Material certificates**

3.1 material

---

**Hygienic approvals and certificates**

3-A, EHEDG, cGMP

---

**Steam****Measuring principle**

Coriolis

---

**Product headline**

Flowmeter with minimized total cost of ownership and a compact, easily accessible transmitter.

Accurate measurement of liquids and gases for a wide range of standard applications.

---

**Marine approvals and certificates**

LR approval, DNV GL approval, ABS approval, BV approval

---

**Density****Measuring principle**

Coriolis

---



## Density

### Product Headline

Flowmeter with minimized total cost of ownership and a compact, easily accessible transmitter.

Accurate measurement of liquids and gases for a wide range of standard applications.

---

### Sensor features

Cost-effective – multi-purpose device; an alternative to conventional volumetric flowmeters. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs.

Compact dual-tube sensor. Medium temperature up to +150 °C (+302 °F).

---

### Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Process pressure up to 100 bar (1450 psi). Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

---

## Density/Concentration

### Measuring principle

Coriolis

---

### Product headline

Flowmeter with minimized total cost of ownership and a compact, easily accessible transmitter.

Accurate measurement of liquids and gases for a wide range of standard applications.

---

## Density/Concentration

### Sensor features

Cost-effective – multi-purpose device; an alternative to conventional volumetric flowmeters. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs.

Compact dual-tube sensor. Medium temperature up to +150 °C (+302 °F).

### Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Process pressure up to 100 bar (1450 psi). Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

### Nominal diameter range

DN 8 to 80 (3/8 to 3")

### Wetted materials

Measuring tube: 1.4539 (904L)

Connection: 1.4404 (316/316L)

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

### Max. measurement error

Mass flow (liquid): ±0.15 % (standard), ±0.10 % (option)

Volume flow (liquid): ±0.15 %

Mass flow (gas): ±0.50 %

Density (liquid): ±0.0005 g/cm<sup>3</sup>

### Measuring range

0 to 180 000 kg/h (0 to 6615 lb/min)

---

**Density/Concentration****Max. process pressure**PN 100, Class 600, 63K

---

**Medium temperature range**-40 to +150 °C (-40 to +302 °F)

---

**Ambient temperature range**

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

---

**Sensor housing material**1.4301 (304), corrosion resistant

---

**Transmitter housing material**AlSi10Mg, coated; stainless steel for hygienic transmitter design

---

**Degree of protection**

Standard: IP66/67, Type 4X enclosure

IP69

---

**Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available"

---

**Outputs**

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

---

**Inputs**

Status input

4-20 mA input

---

---

**Density/Concentration****Digital communication**

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

---

**Power supply**

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

---

**Product safety**

CE, C-tick, EAC marking

---

**Functional safety**

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Marine approvals and certificates**

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

---

**Pressure approvals and certificates**

PED, CRN

---

**Material certificates**

3.1 material

---

**Hygienic approvals and certificates**

3-A, EHEDG, cGMP

---

More information [www.casc.endress.com/8E3B](http://www.casc.endress.com/8E3B)