

# TA572

## Barstock thermowell

Made of drilled barstock material. Mainly used in heavy duty or general purpose applications.



More information and current pricing:

[www.casc.endress.com/TA572](http://www.casc.endress.com/TA572)

### Benefits:

- The extension, the immersion and the tapering lengths as well as the bar dimensions can be chosen according to process requirements
- A wide choice of standard materials is available; additional versions can be ordered according to specification
- Different grades of surface finishing are also available
- The process connection is welded. The thermowell stem shape is conical

### Specs at a glance

- **Max. process pressure (static)** 500 bar (7252 psi)
- **Maximum standard immersion length** 900 mm (35,43")
- **Max. immersion length on request** 5.000 mm (196,85")

**Field of application:** Due to the challenging process conditions by heavy duty applications the load capacity of a thermowell must be calculated exactly. Dye penetration tests, ultrasound test, helium leakage test, pressure endurance test as well as various, non-destructive material tests prove the quality of materials and processing.

## Features and specifications

Thermowell

### Measuring principle

Bar stock Thermowell

## Thermowell

**Characteristic / Application**

metric style  
weld-in process connections  
round extension

---

**Head connection**

internal thread:  
1/2" NPT  
1/2" NPSC

---

**Maximum standard immersion length**

900 mm (35,43")

---

**Max. immersion length on request**

5.000 mm (196,85")

---

**Process connection**

to weld-in

---

**Thermowell root diameter**

22 mm (0,87")  
27 mm (1,06")

---

**Medium contact material**

1.4401 (316)  
1.4404 (316L)  
1.4571 (316Ti)

---

**Wetted part finishing (Ra)**

< 0,8  $\mu\text{m}$  (31,50  $\mu\text{in}$ )  
< 1,6  $\mu\text{m}$  (63,00  $\mu\text{in}$ )

---

**Tip shape**

straight  
conical  
conical tapered

---

## Thermowell

### Temperature range

-200...700 °C (-328...1.292 °F)

---

### Max. process pressure (static)

500 bar (7252 psi)

---

### Max. process pressure at 400 °C

300 bar (4351 psi)

---

More information [www.casc.endress.com/TA572](http://www.casc.endress.com/TA572)