

Thermowell S.A.Style TLSW1



More information and current pricing:

www.casc.endress.com/TLSW1

Benefits:

- For accuracy, the immersion length should be long enough to permit the entire temperature sensitive portion of the thermometer bulb, or the thermocouple element, to project into the temperature medium to be measured.
- Thermocouples have a short sensitive portion and can be used with protection tubes having short immersion lengths. Resistance (RTD) thermometers have sensitive portions between 25 and 50 mm long.
- Generally the material chosen for a specific installation is governed by corrosion conditions to which the thermowell is exposed.

Specs at a glance

- **Max. process pressure (static)** 100 bar (1450 psi)
- **Maximum standard immersion length** 1.000 mm (39,37")
- **Max. immersion length on request** Not defined

Field of application: Generally the material chosen for a specific installation is governed by corrosion conditions to which the thermowell is exposed. In some instances, strength is a primary requirement while corrosion resistance is secondary. For accuracy of the temperature measurement, the immersion length should be long enough to permit the entire temperature sensitive portion of the thermometer bulb, or the thermocouple element, to project into the temperature medium to be measured.

Features and specifications

Thermowell

Measuring principle

Fabricated Thermowell

Thermowell

Characteristic / Application

metric style
threaded process connection
hexagonal extension

Head connection

Internal thread:
NPT 1/2"
G 1/2"

Maximum standard immersion length

1.000 mm (39,37")

Max. immersion length on request

Not defined

Process connection

Thread:
NPT 1/2"
NPT 3/4"
G1/2"

Thermowell root diameter

10 mm (0,39")
12 mm (0,47")
1/4" SCH40
1/4" SCH80

Medium contact material

1.4404 (316L)

Wetted part finishing (Ra)

Not defined

Tip shape

straight

Thermowell

Temperature range

-200...650 °C (-328...1.202 °F)

Max. process pressure (static)

100 bar (1450 psi)

Max. process pressure at 400 °C

46 bar (667 psi)

More information www.casc.endress.com/TLSW1