

Capacitance Level measurement Liquicap FMI52

For continuous level and interface
measurement in liquids - for large measuring
ranges



Benefits:

- Use also in safety systems requiring functional safety to SIL2 in accordance with IEC 61508
- Reliable and universal application thanks to wide range of certificates and approvals
- No calibration necessary (factory preconfiguration). No calibration necessary for media with a conductivity of 100 μ S/cm and higher
- Material in contact with the process made of corrosion-resistant material
- Menu-guided local configuration via plain text display (optional)
- Two-stage overvoltage protection

Specs at a glance

- **Accuracy** repeatability 0,1%
- **Process temperature** -80°C...200°C -112°F...392°F
- **Process pressure absolute / max. overpressure limit** Vacuum ... 100 bar (Vacuum ... 1450 psi)
- **Max. measurement distance** 0.42 m ... 10.0 m (1.38 ft ... 33 ft)
- **Main wetted parts** Insulation material: FEP,PFA 316L

More information and current pricing:

www.ch.endress.com/FMI52

Field of application: Liquicap FMI52 is a reliable fully insulated rope probe for continuous level monitoring in liquids, particularly in small tanks, build-up forming media and extremely high temperatures - especially for large measuring ranges. The measurement is independent of the dielectric constant (dc). Used in conjunction with Fieldgate FXA320 (remote measured value interrogation using Internet

technology), Liquicap is an ideal solution for Inventory Management Solutions.

Features and specifications

Continuous / Liquids

Measuring principle

Capacitive

Characteristic / Application

Fully insulated rope probe, for standard and extreme process conditions (temperature, pressure)

Interface measurement

Interfaces liquid / liquid also with emulsion layers

Specialities

Inactive length

Factory calibrated

short response time by change of value

Supply / Communication

12-36V DC HART

PFM

Accuracy

repeatability 0,1%

Linearity error for conductive liquids

<0,25%

Ambient temperature

-50°C...+70°C

-58°F...+158°F

Process temperature

-80°C...200°C

-112°F...392°F

Continuous / Liquids**Process pressure absolute / max. overpressure limit**

Vacuum ... 100 bar
(Vacuum ... 1450 psi)

Main wetted parts

Insulation material: FEP,PFA
316L

Process connection

G 3/4, G 1, G1 1/2 /NPT 3/4", NPT 1, NPT1 1/2"
Flange from DN25.../ASME 1".../JIS...

Process connection hygienic

Tri-Clamp ISO02852 gap free plated
Dairy coupling
Flush-mounted seal

Sensor length

Total length: 6m (20ft)
Inactive length: max. 2m (7ft)

Max. measurement distance

0.42 m ... 10.0 m
(1.38 ft ... 33 ft)

Communication

4...20mA HART
PFM

Certificates / Approvals

ATEX, FM, CSA, IEC Ex, TIIS, INMETRO, NEPSI, EAC

Safety approvals

SIL

Design approvals

EN 10204-3.1
NACE MR0175

Continuous / Liquids

Hygienic approvals

EHEDG

Marine approval

GL/ ABS/ DNV

Options

Separate housing
gas-tight probe seal

Application limits

Changing, non-conductive
media, conductivity
< 100 $\mu\text{S}/\text{cm}$

Notice the pressure and temperature derating

More information www.ch.endress.com/FMI52