

# Capacitance Point level detection Liquicap FTI52

For liquids that are highly viscous and tend to form build-up - for large measuring ranges



More information and current pricing:

[www.ch.endress.com/FTI52](http://www.ch.endress.com/FTI52)

## Benefits:

- Cost savings thanks to easy and fast commissioning as calibration takes place at the press of a button
- Reliable and safe measurement due to active build-up compensation
- Reliable and universal application thanks to wide range of certificates and approvals
- Short reaction time
- Material in contact with the process made of corrosion-resistant and FDA-listed materials
- Two-stage overvoltage protection
- No need for recalibration after replacing electronics

## Specs at a glance

- **Process temperature** -80 °C ... +200 °C (-112 °F ... +392 °F)
- **Process pressure / max. overpressure limit** Vacuum ... 100 bar (Vacuum ... 1450 psi)

**Field of application:** Liquicap FTI52 is a rope probe for point level detection of liquids that are highly viscous and tend to form build-up. Also used for detection of interface and foam of conductive liquids. Due to its active build-up compensation FTI52 offers maximum reliability and is suited for a wide range of applications thanks to international certificates. The parts in contact with the process are made of corrosion-resistant and FDA-listed materials - this guarantees a high safety standard.

## Features and specifications

---

**Point Level / Liquids****Measuring principle**Capacitive Liquid

---

**Characteristic / Application**Capacitive Rope probe

---

**Specialities**

Interface detection

Foam detection

---

**Ambient temperature**

-50 °C ... +70 °C

(-58 °F ... +158 °F)

With separate housing:

-50 °C ... +120 °C

(-58°F ... +248 °F)

---

**Process temperature**

-80 °C ... +200 °C

(-112 °F ... +392 °F)

---

**Process pressure / max. overpressure limit**

Vacuum ... 100 bar

(Vacuum ... 1450 psi)

---

**Main wetted parts**

Insulation material: FEP, PFA

316L

---

**Process connection**

G 3/4 ... 1 1/2

NPT 3/4 ... 1 1/2

Flange from DN25.../ASME 1".../JIS 10K...

---

**Process connection hygienic**

Tri-Clamp ISO2852 gap free plated

Dairy coupling

Flush mount

---

---

**Point Level / Liquids****Sensor length**

Total length of probe: max 12m (39 ft)

---

**Communication**

2-wire 19-253 VAC

3-wire

PFM

Relay DPDT

DC-PNP

8/16 mA

---

**Certificates / Approvals**

ATEX, FM, CSA, CSA C/US, IEC Ex, TIIS, INMETRO, NEPSI, EAC

---

**Safety approvals**

Overfill prevention WHG

SIL

---

**Design approvals**

EN 10204-3.1

NACE MR0175

---

**Marine approval**

GL/ ABS/ DNV

---

**Options**

Inactive length

Active build-up compensation

Separate housing

---

**Components**

Transmitter

PFM: FTC325, FTC625, FTC470Z, FTC471Z

3-wire:

FTC325

---

## Point Level / Liquids

### Application limits

Notice the pressure and temperature derating.  
Notice for non conductive medium the DK.

---

More information [www.ch.endress.com/FTI52](http://www.ch.endress.com/FTI52)