

# Proline Promass A 300 Coriolis flowmeter

Accurate single-tube flowmeter for lowest flow rates with a compact, easily accessible transmitter



More information and current pricing:

[www.ch.endress.com/8A3C](http://www.ch.endress.com/8A3C)

## Benefits:

- Space-saving installation – compact, lightweight sensor
- Highest product quality – self-drainable measuring tube design in all line sizes
- Optimum process safety – resistant to corrosive ambient conditions and internal clogging
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

## Specs at a glance

- **Max. measurement error** Mass flow (liquid):  $\pm 0.1\%$  Volume flow (liquid):  $\pm 0.1\%$  Mass flow (gas):  $\pm 0.35\%$  Density (liquid):  $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 450 kg/h (0 to 16.54 lb/min)
- **Medium temperature range** -50 to 205 °C (-58 to 401 °F)
- **Max. process pressure** 430.9 bar (6250 psi)
- **Wetted materials** Measuring tube: stainless steel, 1.4435 (316/316L); Alloy C22

**Field of application:** Promass A is ideal for continuous process control in very demanding applications. Its unique self-drainable single-tube system enables accurate measurement of liquids and gases at lowest flow rates and high pressure. With its compact transmitter Promass A 300 offers high flexibility in terms of operation and system integration: access

from one side, remote display, improved connectivity options. Heartbeat Technology ensures measurement reliability and compliant verification.

## Features and specifications

### Density/Concentration

#### Measuring principle

Coriolis

#### Product headline

Single-tube flowmeter for accurate measurement of lowest flow rates with a compact, easily accessible transmitter. Suitable for applications with smallest flow quantities in all industries.

#### Sensor features

Space-saving installation – compact, lightweight sensor. Highest product quality – self-drainable measuring tube design in all line sizes. Optimum process safety – resistant to corrosive ambient conditions and internal clogging. Nominal diameter: DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ " ). Process pressure up to 430.9 bar (6250 psi).

#### Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology. Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

#### Nominal diameter range

DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ " )

#### Wetted materials

Measuring tube: stainless steel, 1.4435 (316/316L); Alloy C22

#### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

---

**Density/Concentration****Max. measurement error**Mass flow (liquid):  $\pm 0.1\%$ Volume flow (liquid):  $\pm 0.1\%$ Mass flow (gas):  $\pm 0.35\%$  Density (liquid):  $\pm 0.0005\text{ g/cm}^3$ 

---

**Measuring range**0 to 450 kg/h (0 to 16.54 lb/min)

---

**Max. process pressure**430.9 bar (6250 psi)

---

**Medium temperature range**-50 to 205 °C (-58 to 401 °F)

---

**Ambient temperature range**-40 to 60 °C (-40 to +140 °F)

---

**Sensor housing material**Stainless steel, 1.4404 (316L)

---

**Transmitter housing material**AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; stainless steel for hygienic transmitter design

---

**Degree of protection**

Compact version: IP66/67, type 4X enclosure.

External WLAN antenna: IP67

IP69

---

**Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

---

---

**Density/Concentration****Outputs**

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

---

**Inputs**

Status input

4-20 mA input

---

**Digital communication**HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus  
RS485, Profinet, Ethernet/IP, OPC-UA

---

**Power supply**

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI

---

**Product safety**

CE, C-TICK

---

**Functional safety**Functional safety according to IEC 61508, applicable in safety-relevant  
applications in accordance with IEC 61511

**Density/Concentration****Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

**Pressure approvals and certificates**

PED, CRN

**Material certificates**

3.1 material

**Hygienic approvals and certificates**

3-A, cGMP

**Gas****Measuring principle**

Coriolis

**Product headline**

Single-tube flowmeter for accurate measurement of lowest flow rates with a compact, easily accessible transmitter. Suitable for applications with smallest flow quantities in all industries.

**Sensor features**

Space-saving installation – compact, lightweight sensor. Highest product quality – self-drainable measuring tube design in all line sizes. Optimum process safety – resistant to corrosive ambient conditions and internal clogging. Nominal diameter: DN 1 to 4 ( $\frac{1}{2}$  to  $\frac{1}{8}$ "). Process pressure up to 430.9 bar (6250 psi).

**Transmitter features**

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology. Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

## Gas

**Nominal diameter range**

DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ " )

**Wetted materials**

Measuring tube: stainless steel, 1.4435 (316/316L); Alloy C22

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

**Max. measurement error**

Mass flow (liquid):  $\pm 0.1$  %

Volume flow (liquid):  $\pm 0.1$  %

Mass flow (gas):  $\pm 0.35$  % Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

**Measuring range**

0 to 450 kg/h (0 to 16.54 lb/min)

**Max. process pressure**

430.9 bar (6250 psi)

**Medium temperature range**

-50 to 205 °C (-58 to 401 °F)

**Ambient temperature range**

-40 to 60 °C (-40 to +140 °F)

**Sensor housing material**

Stainless steel, 1.4404 (316L)

**Transmitter housing material**

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; stainless steel for hygienic transmitter design

**Degree of protection**

Compact version: IP66/67, type 4X enclosure.

External WLAN antenna: IP67

IP69

**Gas****Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

---

**Outputs**

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

---

**Inputs**

Status input

4-20 mA input

---

**Digital communication**

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus  
RS485, Profinet, Ethernet/IP, OPC-UA

---

**Power supply**

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI

---

**Product safety**

CE, C-TICK

---

**Gas****Functional safety**

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

CRN

---

**Material certificates**

3.1 material

---

**Hygienic approvals and certificates**

3-A, cGMP

---

**Liquids****Measuring principle**

Coriolis

---

**Product headline**

Single-tube flowmeter for accurate measurement of lowest flow rates with a compact, easily accessible transmitter. Suitable for applications with smallest flow quantities in all industries.

---

**Sensor features**

Space-saving installation – compact, lightweight sensor. Highest product quality – self-drainable measuring tube design in all line sizes. Optimum process safety – resistant to corrosive ambient conditions and internal clogging. Nominal diameter: DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ "). Process pressure up to 430.9 bar (6250 psi).

---



## Liquids

### Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology. Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

### Nominal diameter range

DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ " )

### Wetted materials

Measuring tube: stainless steel, 1.4435 (316/316L); Alloy C22

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

### Max. measurement error

Mass flow (liquid):  $\pm 0.1$  %

Volume flow (liquid):  $\pm 0.1$  %

Mass flow (gas):  $\pm 0.35$  % Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

### Measuring range

0 to 450 kg/h (0 to 16.54 lb/min)

### Max. process pressure

430.9 bar (6250 psi)

### Medium temperature range

-50 to 205 °C (-58 to 401 °F)

### Ambient temperature range

-40 to 60 °C (-40 to +140 °F)

### Sensor housing material

Stainless steel, 1.4404 (316L)

## Liquids

---

### Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; stainless steel for hygienic transmitter design

---

### Degree of protection

Compact version: IP66/67, type 4X enclosure.

External WLAN antenna: IP67

IP69

---

### Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

---

### Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

---

### Inputs

Status input

4-20 mA input

---

### Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

---

## Liquids

### Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

---

### Hazardous area approvals

ATEX, IECEX, cCSAus, INMETRO, NEPSI

---

### Product safety

CE, C-TICK

---

### Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

---

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

### Pressure approvals and certificates

CRN

---

### Material certificates

3.1 material

---

### Hygienic approvals and certificates

3-A, cGMP

---

More information [www.ch.endress.com/8A3C](http://www.ch.endress.com/8A3C)