

iTEMP TMT31 head mount temperature transmitter

Accurate and reliable process temperature measurements for RTD sensors



Más información y precios actuales:

www.cl.endress.com/TMT31

Ventajas:

- Push-in terminals for fast, tool-free wiring during installation or maintenance
- Simple parametrization via free software tools (requires FXA291 or TXU10)
- Transmitter-sensor matching using Callendar-Van Dusen linearization for critical measurement points
- Improved RTD measurement accuracy up to 0.1 K and long-term stability
- Diagnostics information according to NAMUR NE 107
- Ready-to-use: Factory pre-configured

Resumen de especificaciones

- **Precisión** (Pt100,Pt1000, -50...+250°C) $\leq 0,1$ K
(Pt100,Pt1000, -58...+482°F) $\leq 0,18$ °F

Ámbito de aplicación: The iTEMP TMT31 is a reliable, long-term stable, single-channel 4 to 20 mA temperature transmitter for thermometers with terminal head Form B suited for use in Zone 2 / Div. 2 areas. Individual transmitter-sensor matching with Callendar-Van Dusen linearization further improves your temperature measurement accuracy for RTD sensors. Push-in terminals for quick wiring facilitate installation. The device is available pre-configured or can easily be parametrized using free software tools.

Características y especificaciones

Transmisores de temperatura

Measuring principle

Transmisor de cabezal

Entrada

Pt100

Pt1000

Salida

1 x analog 4-20mA

Suministro de energía auxiliar

10...36 V DC

Comunicación

PC-programmable

Instalación

Terminal head form B

Precisión(Pt100,Pt1000, -50...+250°C) $\leq 0,1$ K(Pt100,Pt1000, -58...+482°F) $\leq 0,18$ ° F**Aislamiento galvánico**

no

Certificación

ATEX II3G Ex ec IIC Gc

CSA C/US General Purpose

CSA C/US NI Cl.I Div.2 Gr.A-D,Ex ec IIC Gc

ATEX II3G Ex ec IIC Gc + CSA C/US Ex ec IIC

Gc

Más información www.cl.endress.com/TMT31