

RA33 Batch Controller

Recording and controlling of batch operations



More information and current pricing:

www.cz.endress.com/RA33

Benefits:

- Fixed and automatic after-run correction for constant, extremely accurate results
- Higher quality through fast and exact dosing
- Optional volume correction for mineral oils as per ASTM D1250-04
- Detailed logging of protocols (preset counter, volume counter, batch name and number) as well as error messages and changes of operating parameters
- Standard models are suitable for connecting and supplying all common flow transmitters, temperature sensors and density sensors
- Remote control option to start and abort batch runs
- Daily, monthly and annual statistics on the batch run size and quantity

Specs at a glance

- **Input** 1 x analogue (I) / pulse (for flow) 1 x RTD (for temperature) 1 x analogue (I) (for density) Loop power supply 24V DC (+/-16%)
- **Output** 1 x analogue (I) / pulse (active) 2 x open collector
- **Display** 160 x 80 Dot-Matrix LCD with white backlit Colour change in case of alarm event Active display area 70 x 34 mm
- **Calculations** Volume calculation

Field of application: The Batch Controller RA33 is designed to record flow and control output signals for valves and pumps to ensure the exact dosing of predefined batch quantities. The measured volume can be corrected with the temperature/density compensation function. The filling process can be optimized with an automatic or fixed after-run correction. Mineral oils can be corrected according to the ASTM D1250-04 standard.

Features and specifications

Energy & Application Manager	Measuring principle Application manager
	Measuring principle Batch controller
	Function Filling & dosing
	Calculations Volume calculation
	Number of applications 1
	Data storage yes
	Calculation standards ASTM D1250-04
	Communication RS232 USB Ethernet Modbus TCP Modbus RTU
	Power supply Not defined
	Loop power supply Low voltage power supply: 100 bis 230 V AC (-15% / +10%) Small voltage power supply: 24 V DC (-50% / +75%) 24 V AC (\pm 50%)

Energy & Application Manager**Protection class**

IP65

Input

1 x analogue (I) / pulse (for flow)
1 x RTD (for temperature)
1 x analogue (I) (for density)
Loop power supply 24V DC (+/-16%)

Output

1 x analogue (I) / pulse (active)
2 x open collector

Dimensions (WxHxD)

144 x 144 x 103.1 mm (5.67" x 5.67" x 4.06")

Operation

3 operation buttons and 14 function buttons for batch operation or via FieldCare
Read out of historical / logged data via Field Data Manager software (SQL database and visualization interface)
Selectable language

Display

160 x 80 Dot-Matrix LCD with white backlit
Colour change in case of alarm event
Active display area 70 x 34 mm

Software functions

Volume calculation
1 or 2 stage operation
Manual and automatic overrun correction
Volume correction factor (VCF) according ASTM D1250-04 for generalized crude oils, refined products and lubricating oils

Energy & Application Manager **Certificates**
CE
CSA GP
NTEP (USA)

Acquisition / Evaluation **Measuring principle**
Batch controller

Function
Filling & dosing

Certification
CE
UL listed
CSA GP

Input
1 x analogue (I) / pulse (for flow)
1 x RTD (for temperature)
1 x analogue (I) (for density)
Loop power supply 24V DC (+/-16%)

Output
1 x analogue (I) / pulse (active)
2 x open collector

Relay output
2 x relay

Auxiliary power supply / Loop power supply
Low voltage power supply:
100 bis 230 V AC (-15% / +10%)
Small voltage power supply:
24 V DC (-50% / +75%), 24 V AC (\pm 50%)

Acquisition / Evaluation**Dimensions (wxhxd)**

144 x 144 x 103.1 mm
(5.67" x 5.67" x 4.06")

Software

Volume calculation
1 or 2 stage operation
Manual and automatic overrun correction
Volume correction factor (VCF) according ASTM D1250-04 for
generalized crude oils, refined products and lubricating oils

Operation

3 operation buttons and 14 function buttons for batch operation or via
FieldCare
Read out of historical / logged data via Field Data Manager software
(SQL database and visualization interface)
Selectable language

Display

160 x 80 Dot-Matrix LCD with white backlit
Colour change in case of alarm event
Active display area 70 x 34 mm

More information www.cz.endress.com/RA33