

# Cerabar T PMC131



More information and current pricing:

[www.de.endress.com/PMC131](http://www.de.endress.com/PMC131)

## Benefits:

- Compact pressure transducer
- Dry capacitance ceramic sensor (Ceraphire)
- Overload-resistant high purity ceramic sensor (99.9% Al<sub>2</sub>O<sub>3</sub>)
- Best fit for vacuum applications and applications with abrasive media

## Specs at a glance

- **Measuring cell** 100mbar...40bar (1.5psi...600psi)

**Field of application:** The Cerabar PMC131 is a price-attractive pressure transmitter with capacitive, oil-free ceramic sensor for absolute and gauge pressure measurement. The compact design offers the following features: Direct system without diaphragm seal, diaphragm overload/vacuum resistant and cable connection via device plug IP65.

## Features and specifications

### Pressure

#### Measuring principle

#### Characteristic

Cost-effective pressure transducer, capacitive ceramic sensor

#### Supply voltage

11...30V DC

#### Reference Accuracy

0,5%

#### Long term stability

0,15% of URL/year

---

**Pressure****Process temperature**

-20°C...100°C  
(-40°F...212°F)

---

**Ambient temperature**

-20°C...85°C  
(-4°F...185°F)

---

**Measuring cell**

100mbar...40bar  
(1.5psi...600psi)

---

**Max. overpressure limit**

60bar (900psi)

---

**Process connection**

Threads

---

**Communication**

4...20mA Analogue

---

**Certificates / Approvals**

ATEX, CSA

---

**Marine approvals**

GL

---

**Specialities**

Ceraphire

---

More information [www.de.endress.com/PMC131](http://www.de.endress.com/PMC131)