

## RTD-Assembly S.A. Style TLSR5



More information and current pricing:

[www.de.endress.com/TLSR5](http://www.de.endress.com/TLSR5)

### Benefits:

- Pt100 measuring element according to IEC 60751 with an accuracy Class A according to IEC 60751 and Band 5 (1/10 DIN)
- Sheath material SS316/L
- Customized immersion length
- Electrical connection by means of a ceramic terminal block or head mounted transmitter with universal inputs, galvanically isolated and various output signals: Analog output 4...20 mA, HART®, PROFIBUS® PA, FOUNDATION Fieldbus™

### Specs at a glance

- **Accuracy** class A acc. to IEC 60751 Band 5 (1/10 DIN)
- **Response time** depending on configuration
- **Max. process pressure (static)** at 20 °C: 10 bar (150 psi) without thermowell
- **Operating temperature range** PT 100: -200 ...600 °C (-328 ...1.112 °F)
- **Max. immersion length on request** up to 2.000 mm (78,74")

**Field of application:** The thermometer is mainly used in the chemical industry but also finds its use in other branches. The device with head transmitter is a complete unit ready for use with enhanced measurement accuracy and reliability compared to directly wired sensors. A variety of process connections and dimensions offer flexible application possibilities.

### Features and specifications

Thermometer

Measuring principle

---

## Thermometer

**Characteristic / Application**

S.A. Style

universal range of application

usable with or without a thermowell

spring loaded for use in thermowell

Options available to construct removable inserts (spare parts)

---

**Thermowell / protection tube**

to use with or without thermowell (can be ordered separately)

---

**Insert / probe**

mineral insulated (MI), flexible

---

**Max. immersion length on request**

up to 2.000 mm (78,74")

---

**Material protection tube/ thermowell**

1.4401 (316)

---

**Optional coating**

Not defined

---

**Process connection**

Fixed thread:

NPT 1/4"

NPT 1/2"

G1/4"

G1/2"

Union nipple:

NPT 1/2"

G1/2"

---

**Tip shape**

rounded

flat

**Thermometer****Operating temperature range**

PT 100:  
-200 ...600 °C  
(-328 ...1.112 °F)

---

**Max. process pressure (static)**

at 20 °C: 10 bar (150 psi) without thermowell

---

**Accuracy**

class A acc. to IEC 60751  
Band 5 (1/10 DIN)

---

**Response time**

depending on configuration

---

**Integration head transmitter**

yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)

---

**Certification**

EN10204 3.1 Material traceability

---

More information [www.de.endress.com/TLSR5](http://www.de.endress.com/TLSR5)