

Promass 80I



More information and current pricing:

www.de.endress.com/80I

Benefits:

- Energy-saving – full bore design enables minimal pressure loss
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Cost-effective – dedicated design for standard applications
- Safe operation – display provides easy readable process information
- Fully industry compliant – IEC/EN/NAMUR

Specs at a glance

- **Max. measurement error** Mass flow (liquid): $\pm 0.15\%$ Volume flow (liquid): $\pm 0.15\%$ Mass flow (gas): $\pm 0.5\%$ Density (liquid): $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 180 000 kg/h (0 to 6600 lb/min)
- **Medium temperature range** -50 to $+150 \text{ }^\circ\text{C}$ (-58 to $+302 \text{ }^\circ\text{F}$)
- **Max. process pressure** PN 100, Class 600, 63K
- **Wetted materials** Measuring tube: Titanium grade 9 Connection: Titanium grade 2

Field of application: The straight single-tube flow meter Promass I is designed for applications requiring low pressure loss and gentle fluid treatment. Combined with the proven Promass 80 transmitter with push buttons, Promass 80I offers a cost effective solution for applications requiring gentle fluid handling.

Features and specifications

Liquids

Measuring principle

Coriolis

Liquids

Product headline

The straight single-tube flowmeter with a compact or remote transmitter. Measuring liquids and gases in applications requiring low pressure loss and gentle fluid treatment.

Sensor features

Energy-saving – full bore design enables minimal pressure loss. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Straight, easy cleanable single-tube system. TMB technology.

Transmitter features

Cost-effective – dedicated design for standard applications. Safe operation – display provides easy readable process information. Fully industry compliant – IEC/EN/NAMUR. 2-line backlit display with push buttons. Device in compact or remote version.

Nominal diameter range

DN 8 to 80 ($\frac{3}{8}$ to 3")

Wetted materials

Measuring tube: Titanium grade 9

Connection: Titanium grade 2

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

Max. measurement error

Mass flow (liquid): ± 0.15 %

Volume flow (liquid): ± 0.15 %

Mass flow (gas): ± 0.5 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 180 000 kg/h (0 to 6600 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Liquids

Medium temperature range

-50 to +150 °C (-58 to +302 °F)

Ambient temperature range

Standard: -20 to +60 °C (-4 to +140 °F)

Option: -40 to +60 °C (-40 to +140 °F)

Sensor housing material

1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Powder-coated die-cast aluminium

1.4301 (304), sheet

CF3M (316L), cast

Degree of protection

IP67, type 4X enclosure. Remote transmitter: IP67, type 4X enclosure

Display/Operation

2-line backlit display with push buttons

Configuration via local display and operating tools possible

Outputs

3 outputs:

0-20 mA (active)/4-20 mA (active/passive)

Pulse/frequency/switch output (passive)

Inputs

Status input

Digital communication

HART

PROFIBUS PA

Power supply

DC 16 to 62 V

AC 85 to 260 V (45 to 65 Hz)

AC 20 to 55 V (45 to 65 Hz)

Liquids

Hazardous area approvals

ATEX, IECEx, FM, CSA, NEPSI

Other approvals and certificates

3.1 material, calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR, SIL
PED, CRN
3-A

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A

Gas

Measuring principle

Coriolis

Product headline

The straight single-tube flowmeter with a compact or remote transmitter. Measuring liquids and gases in applications requiring low pressure loss and gentle fluid treatment.

Gas

Sensor features

Energy-saving – full bore design enables minimal pressure loss. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Straight, easy cleanable single-tube system. TMB technology.

Transmitter features

Cost-effective – dedicated design for standard applications. Safe operation – display provides easy readable process information. Fully industry compliant – IEC/EN/NAMUR. 2-line backlit display with push buttons. Device in compact or remote version.

Nominal diameter range

DN 8 to 80 ($\frac{3}{8}$ to 3")

Wetted materials

Measuring tube: Titanium grade 9
Connection: Titanium grade 2

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

Max. measurement error

Mass flow (liquid): $\pm 0.15\%$
Volume flow (liquid): $\pm 0.15\%$
Mass flow (gas): $\pm 0.5\%$
Density (liquid): $\pm 0.0005\text{ g/cm}^3$

Measuring range

0 to 180 000 kg/h (0 to 6600 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

-50 to $+150\text{ }^\circ\text{C}$ (-58 to $+302\text{ }^\circ\text{F}$)

Gas

Ambient temperature range

Standard: -20 to +60 °C (-4 to +140 °F)

Option: -40 to +60 °C (-40 to +140 °F)

Sensor housing material

1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Powder-coated die-cast aluminium

1.4301 (304), sheet

CF3M (316L), cast

Degree of protection

IP67, type 4X enclosure. Remote transmitter: IP67, type 4X enclosure

Display/Operation

2-line backlit display with push buttons

Configuration via local display and operating tools possible

Outputs

3 outputs:

0-20 mA (active)/4-20 mA (active/passive)

Pulse/frequency/switch output (passive)

Inputs

Status input

Digital communication

HART

PROFIBUS PA

Power supply

DC 16 to 62 V

AC 85 to 260 V (45 to 65 Hz)

AC 20 to 55 V (45 to 65 Hz)

Hazardous area approvals

ATEX, IECEx, FM, CSA, NEPSI

Gas**Other approvals and certificates**

3.1 material, calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR, SIL
PED, CRN
3-A

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A

Density**Measuring principle**

Coriolis

Characteristic / Application

Balanced single-tube system, "Fit-and-Forget"
installation

Design:

Easy to clean, hygienic, careful handling of the medium
- chemically resistant material

Density

Ambient temperature

-20...+65°C
(-4...+140°F)

Process temperature

-50...+150°C
(-58...+302°F)

Process pressure

PN 16...100
CI 150...600
JIS 10...63K

Wetted parts

Titan

Output

4...20 mA
Pulse/Frequency
Status

Certificates / Approvals

ATEX
FM
CSA

Density/Concentration

Measuring principle

Coriolis

Product headline

The straight single-tube flowmeter with a compact or remote transmitter. Measuring liquids and gases in applications requiring low pressure loss and gentle fluid treatment.

Density/Concentration

Sensor features

Energy-saving – full bore design enables minimal pressure loss. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Straight, easy cleanable single-tube system. TMB technology.

Transmitter features

Cost-effective – dedicated design for standard applications. Safe operation – display provides easy readable process information. Fully industry compliant – IEC/EN/NAMUR. 2-line backlit display with push buttons. Device in compact or remote version.

Nominal diameter range

DN 8 to 80 ($\frac{3}{8}$ to 3")

Wetted materials

Measuring tube: Titanium grade 9
Connection: Titanium grade 2

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

Max. measurement error

Mass flow (liquid): ± 0.15 %
Volume flow (liquid): ± 0.15 %
Mass flow (gas): ± 0.5 %
Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 180 000 kg/h (0 to 6600 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

-50 to +150 °C (-58 to +302 °F)

Density/Concentration**Ambient temperature range**

Standard: -20 to +60 °C (-4 to +140 °F)

Option: -40 to +60 °C (-40 to +140 °F)

Sensor housing material1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Powder-coated die-cast aluminium

1.4301 (304), sheet

CF3M (316L), cast

Degree of protectionIP67, type 4X enclosure. Remote transmitter: IP67, type 4X enclosure

Display/Operation

2-line backlit display with push buttons

Configuration via local display and operating tools possible

Outputs

3 outputs:

0-20 mA (active)/4-20 mA (active/passive)

Pulse/frequency/switch output (passive)

InputsStatus input

Digital communication

HART

PROFIBUS PA

Power supply

DC 16 to 62 V

AC 85 to 260 V (45 to 65 Hz)

AC 20 to 55 V (45 to 65 Hz)

Hazardous area approvalsATEX, IECEx, FM, CSA, NEPSI

Density/Concentration

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A

More information www.de.endress.com/80I